



All dimensions are in mm; tolerances according to ISO 2768 m-H

Order-No.	Cable type	a	b	Weight (g/pce)
11W150-204	RG 180 B/U, 2YCY 0.4/2.5, RG 195 A/U, TZC 75024	4.30	1.75	82.2
11W150-206	RG 141 A/U, RG 58 C/U, 2YCCY 0.4/2.5, 2YC(ms)CY 0.4/2.5	5.35	1.75	81.6
11W150-208	RG 223 /U, RG 400 /U, RG 142 B/U	5.50	1.75	81.0
11W150-209	RG 59 B/U, RG 62 A/U, 2YC(ms)CY 0.5/3.0, 2YCY 0.7/4.4, TZC 75005, Flex 6	6.50	1.75	80.6
11W150-211	RG 71 B/U, BT 2003	7.05	1.75	80.0
11W150-212	RG 21 A/U, RG 222 /U, RG 212 /U, RG 6 A/U(75 Ohm), 2YCCY 0.7/4.4	8.24	1.75	79.5
11W150-213	Belden 9248, Koax 12, Belden 9290, 2YCY 0.78/4.8	7.35	1.75	79.8
11W150-215	RG 213 /U, RG 11 A/U, RG 216 /U, RG 214 /U, RG 144/U, HFE 2.2/7.3 RDK	10.90	2.52	75.2
11W150-218	RG 11 A/U, RG 216 /U, RG 144 /U, 1.0/6.6 (2x shield)	10.90	1.75	75.5
11W150-226	Video 1.0/6.6 (1x shield), PK1 1.0/6.6	9.10	1.75	77.8
11W150-2A7	A 62 PE;	9.10	2.52	75.5

Tooling

Crimping tool

11W150-000

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Rong Fang	30/06/05	Sa. Krautenbacher	13.03.14	c00	14-0352	T. Krojer	13.03.14
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de						Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: info@rosenberger.de	
							Page
							1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[11W150-208](#)