



All dimensions are in mm; tolerances according to ISO 2768 m-H

Documents

Instruction for assembly and disassembly of the connectors 23 MV-A008

Material and plating

Connector parts

Body

Material

Luranyl KR 2402

Plating

N/A

Environmental data

Temperature range

-65°C to +115°C

2002/95/EC (RoHS)

compliant

MR capability

non-magnetic

Tooling

Extraction tool for the connectors

23W100-000

Packing

Standard

5 pce in bag

Weight

0.45 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	27/01/09	Armin Maiwlder	02/11/11	c00	11-1011	M. Rahberger	02/11/11
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: info@rosenberger.de		Page 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[23Z121-005](#)