

Technical Data Sheet

Rosenberger

Cable assembly
SMP / SMA – RTK-Flex047

70W-19K1-32K1-XXXXX



All dimensions are in mm; tolerances:
 ≤ 100 : $XXX \pm 2.0$; > 100 to ≤ 1500 : $XXX \pm 5.0$; > 1500 to ≤ 3000 : $XXX \pm 10.0$; > 3000 : $\pm 1.5\%$

Available variants

Type	Max Insertion Loss	Marking	Weight (g) / pce
70W-19K1-32K1-XXXXX	$\leq 0.0057 \text{ dB/mm} * A \text{ mm} + 0.55 \text{ dB}$	ROSENBERGER YYWW 70W-19K1-32K1-XXXXX	$0.0052 \text{ g/mm} * A \text{ mm} + 2.35 \text{ g}$

XXXXX – length in mm = A
WW – week YY – year

Note: max Insertion Loss:
First Constant = Cable attenuation in dB/mm; Second Constant = Connector left and Connector right

Weight:
First Constant = Cable weight per mm; Second Constant = Connector left and Connector right per pce

Assembly parts

Connector left	SMP Jack	19K107-270L5
Connector right	SMA Jack	32K10D-270L5
Cable	RTK-Flex047	

Electrical data

Impedance	50 Ω
Frequency	DC to 18 GHz
Return Loss ¹	$\geq 15 \text{ dB}$, DC to 18 GHz
Insertion Loss ¹	see table available variants

¹ Return Loss and Insertion Loss includes the measurement adaptor

Mechanical data

Minimum bend radius:	
Single	5 mm
Multiple	10 mm

Environmental data

Temperature range	-40°C to +125°C
RoHS	compliant

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Lizzy Beller	01/07/20	Mark Bennett	01/21/20	100	Preliminary	Mark Bennett	01/21/20
Rosenberger North America P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com				Tel. : +1.717.859.8900 Fax : +1.717.859.7044 Email : info@rosenbergerna.com			Page 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Rosenberger:

[70W-19K1-32K1-00152](#) [70W-19K1-32K1-00305](#)