



Contents

Device	Part number	Quantity	Calibration Option ^a
Gauge plug (including gauge block)	P9W00S-000	1	FC
Gauge jack (including gauge block)	P9W00K-000	1	FC

a. See "Declaration of calibration options" for explanation.

Mechanical specifications

Gauge block	0.00 mm
Gauge range	0.00 mm ± 0.5 mm
Scale gradation	1 µm
Limit of measurement error ^{1,2}	≤ 10 µm
Typical measurement error ^{1,2}	≤ 6 µm
Measuring force	0.8 N

¹ When zeroed with gauge block

² 0.12 mm recession to 0.04 mm protrusion

Documentation

This kit is delivered with

- **Calibration Certificate**
Details see "Declaration of calibration options"
- **Operating Manual**

Declaration of calibration options

Factory Calibration

Standard delivery for this gauge includes a Factory Calibration. The Calibration Certificate issued reports individual mechanical calibration results, traceable to national / international standards.

Accredited Calibration

Not available.

For further, more detailed information see application note AN001 on the Rosenberger homepage.

Calibration interval

Recommendation 12 months

For further, more detailed information please visit our homepage www.rosenberger.com.

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
F. Reiner	08.08.17	M. Moder	13.11.18	200	18-v734	M. Knoll	13.11.18

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de	Tel. : +49 8684 18-0 Email : info@rosenberger.de	Page 2 / 2
--	--	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[P9GK0KS-010](#)