




All dimensions are in mm; tolerances according to ISO 2768 m-H

| Order-No.  | Cable type                                                               | a     | b    | Weight (g/pce) |
|------------|--------------------------------------------------------------------------|-------|------|----------------|
| 11W150-204 | RG 180 B/U, 2YCY 0.4/2.5, RG 195 A/U, TZC 75024                          | 4.30  | 1.75 | 82.2           |
| 11W150-206 | RG 141 A/U, RG 58 C/U, 2YCCY 0.4/2.5, 2YC(ms)CY 0.4/2.5                  | 5.35  | 1.75 | 81.6           |
| 11W150-208 | RG 223 /U, RG 400 /U, RG 142 B/U                                         | 5.50  | 1.75 | 81.0           |
| 11W150-209 | RG 59 B/U, RG 62 A/U, 2YC(ms)CY 0.5/3.0, 2YCY 0.7/4.4, TZC 75005, Flex 6 | 6.50  | 1.75 | 80.6           |
| 11W150-211 | RG 71 B/U, BT 2003                                                       | 7.05  | 1.75 | 80.0           |
| 11W150-212 | RG 21 A/U, RG 222 /U, RG 212 /U, RG 6 A/U(75 Ohm), 2YCCY 0.7/4.4         | 8.24  | 1.75 | 79.5           |
| 11W150-213 | Belden 9248, Koax 12, Belden 9290, 2YCY 0.78/4.8                         | 7.35  | 1.75 | 79.8           |
| 11W150-215 | RG 213 /U, RG 11 A/U, RG 216 /U, RG 214 /U, RG 144/U, HFE 2.2/7.3 RDK    | 10.90 | 2.52 | 75.2           |
| 11W150-218 | RG 11 A/U, RG 216 /U, RG 144 /U, 1.0/6.6 (2x shield)                     | 10.90 | 1.75 | 75.5           |
| 11W150-226 | Video 1.0/6.6 (1x shield), PK1 1.0/6.6                                   | 9.10  | 1.75 | 77.8           |
| 11W150-2A7 | A 62 PE;                                                                 | 9.10  | 2.52 | 75.5           |
|            |                                                                          |       |      |                |

## Tooling

Crimping tool

11W150-000

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

| Draft                                                                                                                                                  | Date     | Approved          | Date     | Rev. | Engineering change number                                                                                          | Name      | Date          |
|--------------------------------------------------------------------------------------------------------------------------------------------------------|----------|-------------------|----------|------|--------------------------------------------------------------------------------------------------------------------|-----------|---------------|
| Rong Fang                                                                                                                                              | 30/06/05 | Sa. Krautenbacher | 13.03.14 | c00  | 14-0352                                                                                                            | T. Krojer | 13.03.14      |
| Rosenberger Hochfrequenztechnik GmbH & Co. KG<br>P.O.Box 1260 D-84526 Tittmoning Germany<br><a href="http://www.rosenberger.de">www.rosenberger.de</a> |          |                   |          |      | Tel.: +49 8684 18-0<br>Fax: +49 8684 18-499<br>email: <a href="mailto:info@rosenberger.de">info@rosenberger.de</a> |           | Page<br>1 / 1 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Rosenberger:

[11W150-209](#) [11W150-204](#) [11W150-215](#) [11W150-213](#)