




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to

Rosenberger 28K000-000, series QMA
Rosenberger is an authorised QLF® manufacturer

Documents

N/A

Material and plating**Connector parts**

Center contact
Outer contact
Body
Dielectric

Material

Beryllium copper
Brass
Brass
PTFE

Plating

AuroDur, gold plated
White bronze(e.g. Optalloy®)
White bronze(e.g. Optalloy®)

TECHNICAL DATA SHEET

Rosenberger

ADAPTOR
QMA JACK -JACK

28K101-K00N5

Electrical data

Impedance	50 Ω
Frequency	DC to 18 GHz
Return loss	≥ 32 dB, DC to 3 GHz ≥ 28 dB, 3 to 6 GHz
Insertion loss	≤ 0.05 x $\sqrt{f(\text{GHz})}$ dB, DC to 6 GHz
Insulation resistance	≥ 5 x10 ³ MΩ
Center contact resistance	≤ 3 mΩ
Outer contact resistance	≤ 2.5 mΩ
Test voltage, at sea level, 50Hz	1000 V rms
Working voltage, at sea level, 50Hz	480 V rms
RF-leakage	≥ 95 dB up to 2 GHz ≥ 80 dB up to 4 GHz ≥ 70 dB up to 6 GHz
Intermodulation (3 rd order)	≤ -120 dBc @ 2 x 20 W

Mechanical data

Mating cycles	min. 100
Center contact captivation: axial	≥ 20 N
Engagement force	typ. 25 N
Disengagement force	typ. 20 N
Retention force for interface	60 N min.

Environmental data

Temperature range	-40°C to +85°C
Storage temperature	-40°C to +85°C
Thermal shock	IEC 60169-1 16.4 (-40 / +85°C)
Corrosion	IEC 60169-1 16.7 (48 hrs)
Vibration	IEC 60068-2-64 random
Damp heat, steady state	IEC 60169-1 16.3 (96 hrs)
RoHS	compliant

Tooling

N/A

Suitable cables

N/A

Weight

Weight	3.2 g/pce
--------	-----------

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Inge Mühlauer	05/10/04	Sa. Krautenbacher	13.03.14	d00	14-0352	T. Krojer	13.03.14
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: info@rosenberger.de		Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[28K101-K00N5](#)