




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
Mechanically compatible with

IEC 60169-23
RPC-2.92 and SMA

Documents

N/A

Material and plating

Connector parts

Center contact
Outer contact
Coupling nut

Material

Beryllium copper
Brass
Stainless steel

Plating

Gold, min. 1.27 μm , over chemical nickel
Gold, min. 1.27 μm , over chemical nickel
Passivated

Electrical data

Impedance	50 $\Omega \pm 0.35 \Omega$
Frequency	0.3 GHz to 26.5 GHz
Return loss	≥ 40 dB, 0.3 GHz to 4 GHz ≥ 35 dB, 4 GHz to 26.5 GHz
Insertion loss	≤ 0.12 dB at 26.5 GHz
Center contact resistance	≤ 3.0 m Ω
Outer contact resistance	≤ 2.0 m Ω

Mechanical data

Mating cycles	≥ 500
Coupling test torque	1.70 Nm
Recommended torque	0.80 Nm to 1.10 Nm
Airline dimensions:	
- Outer diameter	3.500 mm ± 0.005 mm
- Inner diameter	1.520 mm ± 0.005 mm
- Length outer contact	38.50 mm ± 0.02 mm
- Length center contact	38.50 mm $- 0.02$ mm
- Difference (outer/center-contact)	max. 0.04 mm

Environmental data

Temperature range	-40°C to +85°C
Thermal shock	MIL-STD-202, Method 107, Condition B
Corrosion	MIL-STD-202, Method 101, Condition B
Vibration	MIL-STD-202, Method 204, Condition D
Shock	MIL-STD-202, Method 213, Condition I
Moisture resistance	MIL-STD-202, Method 106
2002/95/EC (RoHS)	compliant

Tooling

N/A

Suitable cables

N/A

Packing

Standard	1 pce in box
Weight	9.3 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	14/07/04	Armin Maiwaelder	29/06/07	d00	07-0277	Manuela Fuehrich	29/06/07
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: info@rosenberger.de			Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[03S101-K038](#)