



All dimensions are in mm; tolerances according to ISO 2768 m-H

Order-No.	Cable type	a	Weight (g/pce)
11W150-101	RG 178 B/U, RG 196 A/U	2.75	62.8
11W150-102	RG 316 /U, RG 174 A/U, RG 188 A/U, RG 179 B/U, RG 187 A/U	3.30	62.5
11W150-103	RG 316 /U-d, K02252d, RG 179 B/U-d, 2XCCX 0.45/1.5, 06YC(St)06Y 0.4/1.6	3.63	62.4
11W150-104	RG 180 B/U, 2YCY 0.4/2.5, RG 195 A/U, TZC 75024	4.30	62.0
11W150-106	RG 141 A/U, RG 58 C/U, 2YCCY 0.4/2.5, 2YC(ms)CY 0.4/2.5	5.35	61.7
11W150-108	RG 223 /U, RG 400 /U, RG 142 B/U	5.50	61.5
11W150-109	RG 59 B/U, RG 62 A/U, 2YC(ms)CY 0.5/3.0, 2YCY 0.7/4.4, TZC 75005, Flex 6	6.50	61.2
11W150-115	RG 213 /U, RG 11 A/U, RG 216 /U, RG 214 /U, RG 144 /U, HFE 2.2/7.3 RDK	10.90	56.1
11W150-126	Video 1.0/6.6 (1x shield), PKI 1.0/6.6	9.10	58.5
11W150-150	BT 2001, Flex 3-75, 02Y(St)CY 0.45/2.0	4.55	61.9
11W150-1V6	TZC 75024, TZC 75025, BT 3002	4.95	61.8

**Tooling**

Crimping tool

11W150-000

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Rong Fang	30/06/05	Sa. Krautenbacher	13.03.14	c00	14-0352	T. Krojer	13.03.14
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany <a href="http://www.rosenberger.de">www.rosenberger.de</a>					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: <a href="mailto:info@rosenberger.de">info@rosenberger.de</a>		Page 1 / 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[11W150-000](#)