


Compact format, robust keyboard  
with integrated trackball



- Vandal resistant  
(10J BS EN 60068-2-75: 1997)
- Weather resistant (IP54)
- With factory fitted 2.5m USB 2.0 cable
- Optional fixing kit for under panel installation or adapter kit for benchtop use (both sold separately)
- RFI/EMI Protection in accordance with current European and US directives
- Operational life of more than 4 million cycles per key
- Resistant to most commonly used cleaning agents
- Integral 38mm trackball with left & right click keys
- 63 keys
- Compact format:  
360mm x 118.5mm x 438.5mm



Storm Interface products include technology protected by international patents and design registration. All rights reserved.

[www.storm-interface.com](http://www.storm-interface.com)






## 2210-T/B Robust Keyboard for Industrial & Public Environments

Robust, high contrast keyboard for use in public access and industrial installations. This responsive and reliable keyboard was developed specifically for use in unsupervised or semi-supervised environments where hardware may be subject to hard use or abuse. The 2210 Robust keyboard was designed to provide maximum systems accessibility to those with sensory or mobility impairments. Ideal for use in kiosk and retail applications.

### Overall Dimensions



### Specifications

|                                |                                      |
|--------------------------------|--------------------------------------|
| Keyboard Weight                | 1.80kg                               |
| with polymer keytops/trackball |                                      |
| Underpanel cut-out aperture    | 11.0 x 4.3in.<br>(351.00 x 109.50mm) |
| Max panel thickness            | (2mm)                                |

### Options

|             |   |
|-------------|---|
| Build Style | Robust (black polymer top plate)                    |
| Keytops     | White keytops, laser marked black                   |
| Encoder     | USB 2.0   |
| Languages   | English UK, English USA,<br>French, Spanish, German |
| Cable       | Factory Fitted 2.5m USB 2.0                         |


### Electrical

|                                 |  |
|---------------------------------|--|
| EMC Emissions                   | EN55022 : 1998 Class B Limit           |
| EMC Immunity to ESD             | EN55024 : 1998                         |
| EMC Immunity to Radiated Fields | EN55024 : 1998                         |
| Electrical Safety               | EN60950, UL60950                       |
| Communication                   | Industry Standard<br>USB 2.0 Interface |

|                     |                                |
|---------------------|--------------------------------|
| Supply requirements |                                |
| – voltage           | +5V nominal (5.5V to 4.75V)    |
| Supply requirements |                                |
| – current           | 60mA (with 2 LEDs illuminated) |

### Environmental

|                                |                                 |
|--------------------------------|---------------------------------|
| Sealing – Water / Particulates | EN60529 (sealing to IP54)       |
| Trackball sealing              | IP54 stationary (IP54 rotating) |
| Temperature                    | -20°C to +60°C operating (dry)  |



View showing rear of panel with dimensions of stud positions and panel cut out details

All dimensions in mm.

### Mechanical

|                   |                                      |
|-------------------|--------------------------------------|
| Impact Resistance | 10 Joules via 50mm dia steel striker |
| Key Pitch         | 19mm                                 |
| Size              | 11mm square                          |
| Travel            | 1.5mm nominal                        |
| Actuation Force   | 100g nominal                         |

### Accessories

|                           |               |
|---------------------------|---------------|
|                           | Stock Code    |
| 2200 Underpanel           | 2210-MK000[x] |
| Fixing Kit                |               |
| contains clips            |               |
| 2200 Foot Kit             | 220-FK000[x]  |
| required for benchtop use |               |

[www.storm-interface.com](http://www.storm-interface.com)

Storm is a trademark  
of Keymat Technology Ltd  
Storm Interface is a trading name  
of Keymat Technology Ltd

Storm Interface products include  
technology protected by international  
patents and design registration.  
All rights reserved.

Designed & produced by NIK Design  
nik@nikdesign.co.uk

Whilst every effort is made to ensure details  
are correct at time of print, specifications are  
subject to change without notice.



UL File reference: E230121

2210-TB-Robust-LIT-01 Rev 1 Mar 2011



FM 39602

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Storm Interface:](#)

[2210-452223](#)