

CHERRY DW 3000



Models may vary from the image shown

Best price/performance ratio for office users

CHERRY DW 3000 is rock-solid CHERRY technology with an excellent price/performance ratio. Modern, flat design with gentle, quiet and durable abrasion-resistant keys. Universal, reliable and optimized for professional use.

Key benefits

- Flat, wireless keyboard including cursor and number pad
- Whisper keystroke keys with durable key inscription
- Up to 10 million keystrokes
- 4 hotkeys (calculator, e-mail, browser, sleep mode)
- Plug & Play via USB connection
- 3-button mouse, for both left-handed and right-handed operation
- Optical sensor technology (1,200 dpi)
- Battery status display in keyboard and mouse
- Almost interference-free wireless 2.4 GHz technology (range of up to 10 metres)
- Nano USB receiver
- GS approval

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

502 g (keyboard with battery), 85 g (mouse with battery), 1.5 g (receiver)

Total weight (with packaging):

923 g

Transmission range:

approx. 10 m

Frequency range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-20°C to 65°C

Operating Temperature:

0°C to 50°C

Current Consumption:

typ. 3 mA (keyboard), typ. 6 mA (mouse), max. 35 mA (receiver)

Interface:

- USB

Product approvals:

- c-tick
- UL
- CE
- FCC
- TÜV-Süd/GS
- UKCA



System requirements:

- USB connection

Delivery Volume:

- Operating instructions in hard copy
- 1 battery (type AA)
- 1 optical wireless mouse
- 1 wireless keyboard
- 1 nano USB transmission receiver
- 1 battery (type AAA)

Dimensions (product):

458 x 170 x 20 mm (keyboard), 109 x 62 x 37 mm (mouse), 18 x 13 x 5 mm (receiver)

Packaging dimensions:

549 x 200 x 45 mm

Reliability:

- MTBF > 45,000 hours

Mouse:

- Scanning: Infrared
- Resolution: 1200 dpi
- Number of Keys: 3
- Mouse wheel design: Scroll wheel with key function
- Design: Symmetrical
- Connection: wireless
- Scanning rate: max. 2400/s
- Housing colour: Product dependant, see table "Models"
- Key colour: Product dependant, see table "Models"

Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of additional keys: 4

Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 24

Warranty:

3-year limited manufacturer's guarantee

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Number of Keys	Mouse Housing colour	Mouse Key colour
1	CHERRY DW 3000	JD-0710BE-2	4025112094460	Belgium	black	black	105+4	anthracite	black
2	CHERRY DW 3000	JD-0710BU-2	4025112097126	Bulgaria	black	black	105+4	anthracite	black
3	CHERRY DW 3000	JD-0710CS-2	4025112088513	Czech Republic / Slovakia	black	black	105+4	anthracite	black
4	CHERRY DW 3000	JD-0710DE-0	4025112088490	Germany	pale grey	pale grey	105+4	pale grey	pale grey
5	CHERRY DW 3000	JD-0710DE-2	4025112088414	Germany	black	black	105+4	anthracite	black
6	CHERRY DW 3000	JD-0710ES-2	4025112088452	Spain	black	black	105+4	anthracite	black
7	CHERRY DW 3000	JD-0710EU-2	4025112088438	US English with EURO symbol	black	black	104+4	anthracite	black
8	CHERRY DW 3000	JD-0710FR-2	4025112088445	France	black	black	105+4	anthracite	black
9	CHERRY DW 3000	JD-0710GB-2	4025112088421	UK	black	black	105+4	anthracite	black
10	CHERRY DW 3000	JD-0710HU-2	4025112088476	Hungary	black	black	105+4	anthracite	black
11	CHERRY DW 3000	JD-0710IT-2	4025112088469	Italy	black	black	105+4	anthracite	black
12	CHERRY DW 3000	JD-0710PN-2	4025112088483	Pan-Nordic	black	black	105+4	anthracite	black
13	CHERRY DW 3000	JD-0710SL-2	4025112092077	Slovenia	black	black	105+4	anthracite	black

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

JD-0710EU-2