

CHERRY KC 6000C FOR MAC

Corded Mac Keyboard



Models may vary from the image shown

Ultra-flat design keyboard with Mac layout and USB-C connection

The wired KC 6000C FOR MAC is the perfect companion for frequent typists on a MAC.

The keyboard with a 5.9 ft long cable and Mac layout scores with 13 special functions arranged on the F-keys such as Mission Control, Spotlight Search, screen brightness, Lock PC and media control. They are executed directly. To access the default functions on the F-keys, hold down the FN key and select the appropriate key. If you want to run the standard functions permanently, press the Control and FN keys at the same time. The FN LED in the F14 key lights up when the FN key is locked.

Even users with high demands will get long-term enjoyment from the KC 6000C FOR MAC. The in-house CHERRY SX scissor technology ensures highly comfortable and quiet typing. Users who like to write on laptop keyboards will feel particularly at home with the chiclet design keys right away. With the help of the computer keyboard's numeric keypad, frequent input of numbers becomes effortless. The compact slim keyboard also has an in-built metal plate, making it stable and non-slip on your desk. Thanks to the rubber feet (included), the keyboard can be easily adjusted to the individual user's preferred angle.

The CHERRY KC 6000C FOR MAC is a high-quality alternative to other Mac keyboards. The flat Mac keyboard is a gain for the desk on every level. The flat cable keyboard can be used on all end devices with a USB-C connection and operating system MAC OS X 10.13 and higher. With plastic-free packaging, the keyboard scores highly environmentally too.

Decisive advantages

- Keyboard in chiclet design with Mac layout
- 5.9 ft cable with USB-C connection
- Quick access to 13 frequently used Mac functions
- Compact and slim housing
- Precise scissor mechanism for an ideal operating feeling
- High weight due to integrated metal plate
- Exceptional design with shimmering blue key frame
- Durable key labels
- Numeric keypad for convenient number input
- Rubber feet for height adjustment for ergonomic writing

Errors, technical changes and delivery options reserved. Technical information refers only to the specifications of the products. Features may differ from the information provided.

CHERRY KC 6000C FOR MAC

Corded Mac Keyboard

Technical specifications

Layout (country or language)

Depends on product, see "Models" table

Housing color

Silver

Key color

White

Weight (product)

approx. 1.46 lbs

Total weight (with packaging)

approx. 1.93 lbs

Cable length

approx. 5.9 ft

Storage temperature

-4 °C to 140 °F

Operating temperature

32 °C to 104 °F

Power consumption

max. 15 mA

Connection

USB-C

Product approvals

- CE
- UL
- FCC
- UKCA
- China RoHS

System requirements

USB-C connection

MAC OS X 10.13 or higher

Scope of delivery

- CHERRY KC 6000C FOR MAC
- Operating instructions in hard copy

Product dimensions

approx. 17.32 x 5.12 x .59 in

Packaging dimensions

approx. 17.83 x 6.69 x 1.29 in

Keyboard

- Key technology: SX
- Service life of standard key > 10 million strokes
- Number of buttons: Depends on product, see "Models" table

Packaging unit

- Number of products in outer package 10
- Number of outer packages per pallet 20

Warranty

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below. Statutory warranty applies for the first two years following delivery. For the third year following delivery, CHERRY voluntarily provides an additional warranty in accordance with the following conditions ("Extended Warranty"). Please contact the seller of your CHERRY product in the event of a defect. Do not try to repair the product yourself and do not open the product. Warranty is not granted in the event that unauthorized changes to the product cause a defect.

Extended Warranty Conditions

In the event that a defect occurs after the first 2 years following the product's delivery have elapsed, CHERRY grants its customers the right to assert subsequent performance claims, i.e. repair or redelivery, for a further period of one year. The extended warranty must be asserted against the seller of the CHERRY product accompanied by the original invoice, proof of purchase or comparable proof of the time of purchase.

In extended warranty cases, CHERRY shall repair the defects, with the involvement of the respective dealer if necessary, provided that the customer is justified in its claim for subsequent performance.

Damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas, are excluded from the extended warranty. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

CHERRY KC 6000C FOR MAC

Corded Mac Keyboard

Design variants

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Number of keys
1	CHERRY KC 6000C FOR MAC	JK-1620DE-1	4025112099731	Germany	105 + 6
2	CHERRY KC 6000C FOR MAC	JK-1620FR-1	4025112099939	Belgium/France	105 + 6
3	CHERRY KC 6000C FOR MAC	JK-1620GB-1	4025112099946	Great Britain	105 + 6
4	CHERRY KC 6000C FOR MAC	JK-1620PN-1	4025112099663	Pan-Nordic	105 + 6
5	CHERRY KC 6000C FOR MAC	JK-1620US-1	840183606183 (UPC)	US	104 + 6
6	CHERRY KC 6000C FOR MAC	JK-1620CN-1	4025112099632	CN-Layout	104 + 6

Please contact your local CHERRY Service and Support team or your CHERRY sales partner to find out which versions are available in your country.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CHERRY:](#)

[JK-1620US-1](#)