

CHERRY KW 9100 SLIM FOR MAC

Wireless Mac Keyboard



Models may vary from the image shown

The wireless and rechargeable accessory for Mac users with an affinity for design

The low-profile wireless keyboard with the Mac layout will not only cater to the demands of discerning Mac users – its smart technical features and the workmanship are also second to none.

FN Lock is used to enjoy permanent access to 13 frequently used Mac functions, such as Mission Control, Spotlight Search, screen brightness, lock PC and media controls. If FN Lock is not activated, the keyboard simply performs the F key commands. A brief glance at the FN Lock LED will suffice to determine whether FN Lock is activated or not. If caps lock is activated or the rechargeable battery is running low, this is also indicated by the LEDs.

The extra-slim keyboard has a range of up to 10 m when connected using Bluetooth® or the 2.4 GHz wireless USB receiver included with it. The slide switch on the keyboard allows you to change from one transmission type to the other with ease. For example, you can connect a laptop using Bluetooth® and an additional PC using wireless. AES-128 also encrypts the data being transmitted.

The wireless and low-profile keyboard with the Mac layout comes with a USB-A to USB-C cable. If the rechargeable battery starts running low following several weeks of reliable operation, the slim wireless keyboard can be charged at any free socket while you continue working uninterrupted.

User convenience was a particular focus when the CHERRY KW 9100 SLIM FOR MAC was developed. The high-quality CHERRY SC scissor technology with low key travel is the key to optimal typing comfort and quiet operation. The angle at which the wireless keyboard is positioned is very easy to adapt using a removable magnetic strip. An integrated metal plate ensures stability.

If you're looking for a high-quality and esthetically pleasing alternative to conventional keyboards for a Mac, then you've found the right address with the CHERRY KW 9100 SLIM FOR MAC. The wireless computer keyboard can be used with all Mac computers with a USB connection for the USB wireless receiver, or with all Bluetooth® receivers featuring version 4.0 or higher when the Bluetooth® interface is used*. An added bonus for the environment: The packaging includes no plastic at all. An added bonus is that the packaging includes no plastic at all.

*Lock key with MAC OS X 10.13 or higher.

The most important advantages

- Design: Chiclet layout with numeric keypad
- Key technology: SX
- Service life of standard key: > 10 million strokes
- Magnetic support bar for inclination adjustment
- Power supply: rechargeable lithium-ion battery with 650 mAh (permanently installed)
- Status display: Caps lock, FN and battery status (by LED in keys), Bluetooth® connection, wireless and battery charge status (bi-color LED)
- Number of buttons: Depends on product, see table
- Number of extra keys: 13
- Additional key functions: Increase/reduce screen brightness, Mission Control, Spotlight, previous track, play/pause, next track, mute, increase/reduce volume, lock PC (MAC OS X 10.13 or higher), CD eject, zoom in/out

CHERRY KW 9100 SLIM FOR MAC

Wireless Mac Keyboard

Technical specifications

Layout (country or language)

Depends on product, see "Models" table

Housing color

Silver

Key color

White

Weight (product)

Keyboard: approx. 675 g (incl. battery + magnetic bar)

Receiver: approx. 2 g

Cable: approx. 25 g

Total weight (with packaging)

approx. 860 g

Storage temperature

-20 °C to 60 °C

Operating temperature

0 °C to 40 °C

Power consumption

Max 5 mA

Connection

USB

Product approvals

- CE
- UL
- FCC
- UKCA
- China RoHS

System requirements

MAC OS X 10.13 or higher

Via Bluetooth®: device compatible with min. Bluetooth® 4.0 or higher

Via USB: free USB port (type A)

Scope of delivery

- CHERRY KW 9100 SLIM FOR MAC
- Operating instructions in hard copy

Product dimensions

approx. 440 x 130 x 15 mm

Packaging dimensions

approx. 453 x 170 x 33 mm

Keyboard

- Key technology: SX
- Service life of standard key: > 10 million strokes
- Number of buttons: Depends on product, see "Models" table

Packaging unit

- Number of products in outer package 10
- Number of outer packages per pallet 20

Warranty

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below. Statutory warranty applies for the first two years following delivery. For the third year following delivery, CHERRY voluntarily provides an additional warranty in accordance with the following conditions ("Extended Warranty"). Please contact the seller of your CHERRY product in the event of a defect. Do not try to repair the product yourself and do not open the product. Warranty is not granted in the event that unauthorized changes to the product cause a defect.

Extended Warranty Conditions

In the event that a defect occurs after the first 2 years following the product's delivery have elapsed, CHERRY grants its customers the right to assert subsequent performance claims, i.e. repair or redelivery, for a further period of one year. The extended warranty must be asserted against the seller of the CHERRY product accompanied by the original invoice, proof of purchase or comparable proof of the time of purchase.

In extended warranty cases, CHERRY shall repair the defects, with the involvement of the respective dealer if necessary, provided that the customer is justified in its claim for subsequent performance.

Damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas, are excluded from the extended warranty. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery options reserved. Technical information refers only to the specifications of the products. Features may differ from the information provided.

CHERRY KW 9100 SLIM FOR MAC

Wireless Mac Keyboard

Design variants

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Number of keys
1	CHERRY KW 9100 SLIM FOR MAC	JK-9110DE-1	4025112099656	Germany	105 + 6
2	CHERRY KW 9100 SLIM FOR MAC	JK-9110FR-1	4025112099687	Belgium/France	105 + 6
3	CHERRY KW 9100 SLIM FOR MAC	JK-9110GB-1	4025112099694	Great Britain	105 + 6
4	CHERRY KW 9100 SLIM FOR MAC	JK-9110PN-1	4025112099724	Pan-Nordic	105 + 6
5	CHERRY KW 9100 SLIM FOR MAC	JK-9110US-1	840183606114 (UPC)	USA	104 + 6
6	CHERRY KW 9100 SLIM FOR MAC	JK-9110CN-1	4025112099748	CN-Layout	104 + 6

Please contact your local CHERRY Service and Support team or your CHERRY sales partner to find out which versions are available in your country.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

JK-9110US-1