

CHERRY DC 2000



Models may vary from the image shown

Corded Business Desktop Combo With Uncompromised CHERRY Quality

The CHERRY DC 2000 is focused on the core business - office work. With durability, precision and reliability, this wired desktop set is equipped for all tasks in the demanding day-to-day office environment.

Key Benefits

- Optimized for professional use in the office
- Wired mouse with 3 keys and scroll wheel
- Symmetrical design in standard size - suitable for left- and right-handed users
- Mouse Resolution 1,200 dpi
- Flat, corded keyboard with durable key inscription
- 4 hotkeys (calculator, e-mail, browser, sleep mode)
- 3 blue status LEDs
- Up to 10 million keystrokes
- Plug & Play via 1 USB connection for keyboard and for mouse
-

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing Color:

black

Key Color:

black

Weight (product):

530 g/1.17 lb (keyboard), 90 g/3.17 oz (mouse)

Total Weight (with packaging):

896 g / 1.98 lb

Cable Length:

approx. 1.80 m/5.91 ft (keyboard) , approx. 1.80 m/5.91 ft (mouse)

Storage Temperature:

-20°C to 65°C / -4° F to 149° F

Operating Temperature:

0°C to 50°C / 32° F to 122° F

Current Consumption:

max. 50 mA (keyboard), max. 50 mA (mouse)

Interface:

- USB

Product Approvals:

- C-Tick
- UL
- CE
- FCC
- TÜV-Süd/GS



System Requirements:

- USB connections for keyboard and mouse

Box Contents:

- Operating instructions in hard copy
- 1 corded keyboard
- 1 corded mouse

Dimensions (product):

458 x 170 x 20 mm (keyboard), 109 x 62 x 37 mm (mouse) / 18.03 x 6.69 x .79 in (keyboard), 4.29 x 2.44 x 1.46 in (mouse)

Packaging Dimensions:

546 x 198 x 45 mm / 21.5 x 7.80 x 1.77 in

Reliability:

- MTBF > 45,000 hours

Mouse:

- Scanning: Optical
- Resolution: 1200 dpi
- Number of Keys: 3
- Mouse Wheel Design: Scroll wheel with key function
- Design: Symmetrical
- Connection: USB
- Housing Color: black
- Key Color: black

Keyboard:

- Key Technology: LPK
- Service life, standard key: > 10 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of Additional Keys: 4

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 18

Warranty:

3-year limited manufacturer's guarantee

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the

product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product Name	Order Number	EAN Code	Layout (country or language)	Number of Keys
1	CHERRY DC 2000	JD-0800BE-2	4025112083280	Belgium	105+4
2	CHERRY DC 2000	JD-0800BU-2	4025112097119	Bulgaria	105+4
3	CHERRY DC 2000	JD-0800CS-2	4025112085772	Czech Republic / Slovakia	105+4
4	CHERRY DC 2000	JD-0800DE-2	4025112083297	Germany	105+4
5	CHERRY DC 2000	JD-0800ES-2	4025112083303	Spain	105+4
6	CHERRY DC 2000	JD-0800EU-2	4025112084744	US English with EURO symbol	104+4
7	CHERRY DC 2000	JD-0800FR-2	4025112083310	France	105+4
8	CHERRY DC 2000	JD-0800GB-2	4025112083327	UK	105+4
9	CHERRY DC 2000	JD-0800HU-2	4025112086144	Hungary	105+4
10	CHERRY DC 2000	JD-0800PN-2	4025112085048	Pan-Nordic	105+4
11	CHERRY DC 2000	JD-0800SL-2	4025112092091	Slovenia	105+4
12	CHERRY DC 2000	JD-0800TQ-2	4025112086557	Turkey	105+4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

[JD-0800EU-2](#)