

J82-16001 K-1 Series Business Keyboards



**Reliable Business Keyboard
with Compact Durable Package**

Not recommended for new designs, we suggest our JK-0800EU.

Key Features

- Comfortable Key Action
- Space-efficient Compact Keyboard
- Abrasion-proof Writing on Keycaps

Main Part Numbers

J82-16001LUNEU-0
Light grey color, USB interface

J82-16001LUNEU-2
Black color, USB interface

J82-16001LPNEU-0
Light grey color, PS/2 interface

J82-16001LPNEU-2
Black, PS/2 interface

Technical Data

Interface
USB or PS/2 Interface

Current Input
typ. 40 mA

Number of Keys
104 position US Key Layout

Cable Length
approx. 1.80 m

Weight
approx. 650 g (keyboard)
approx. 780 g (with packaging)

Dimensions
approx. 460 x 165 x 32 mm (keyboard)
approx. 485 x 190 x 36 mm (packaging)

Packaging Units
10 keyboards per master carton
20 master cartons per pallet

Keyswitch Lifetime
>10 million operations

Storage Temperature
-20 °C to 60 °C

Operating Temperature
0 °C to 50 °C

Agency Approvals
FCC, CE, C-Tck cURus, GHOST-R,
Microsoft Windows™ XP

Delivery Volume
Keyboard, Printed

Warranty
2 years

Contact

Call, fax or visit our website for more information.

Last Update 3/4/2014

ZF Electronic Systems Pleasant Prairie, LLC
11200 88th Avenue
Pleasant Prairie, WI 53158
Phone: 262.942.6500
Web: www.cherrycorp.com

E-Mail: keyboardsupport@zf.com
Fax: 262.942.6500



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CHERRY:](#)

[J82-16001LPNEU-0](#) [J82-16001LUNEU-2](#) [J82-16001LPNEU-2](#) [J82-16001LUNEU-0](#)