

## CHERRY KC 6000 SLIM FOR MAC

### Corded Mac Keyboard



*Models may vary from the image shown*

### Ultra-flat designer keyboard with Mac layout

The corded KC 6000 SLIM FOR MAC is the streamlined keyboard alternative for avid writers using Mac!

The chiclet design keyboard has 12 functions that make it easy to use on your Mac every day. Frequently used functions (such as screen lock, screen brightness, mission control and media control) can be accessed with a single keystroke.

Compact dimensions leave enough space on your desk for other equipment. The scissor mechanism is practically silent and provides an excellent typing experience and a long service life. The numeric keypad means the keyboard is well prepared for frequent number entries.

A built-in metal plate keeps the keyboard stable and non-slip on your desk. If you prefer a steeper angle when typing, the angle of inclination of the KC 6000 SLIM FOR MAC can be adjusted with 4 rubber feet supplied. A flexible cable allows connection under the desk.

The CHERRY KC 6000 SLIM FOR MAC with silver housing and white keys can be used on all end devices with USB-A connection and MAC OSX operating system.

### Key Benefits

- Keyboard in chiclet design with Mac layout
- Quick access to 12 frequently used Mac functions
- Compact and slim housing
- Precise scissor mechanism for an ideal operating feeling
- High weight due to integrated metal plate
- Exceptional design with shimmering blue key frame
- Abrasion-resistant laser marking
- Numeric keypad for convenient number input
- Rubber feet for height adjustment for ergonomic writing
- 1.8 m cable with USB connection

Errors, technical changes and delivery delays may occur.  
Technical information refers only to the specifications of the products. Features may differ from the information provided.

# CHERRY KC 6000 SLIM FOR MAC

Corded Mac Keyboard

## Technical Data

### Layout (country or language)

Product dependant, see table "Models"

### Housing color

Silver

### Key color

white

### Weight (product)

approx. 660 g / 1.46 lb

### Total Weight (with packaging)

approx. 875 g / approx. 1.93 lb

### Cable Length

approx. 1.80 m / approx. 5.91 ft

### Storage Temperature

-20°C to 60°C / -4° F to 140° F

### Operating Temperature

0°C to 40°C / 32° F to 104° F

### Current Consumption

typ. 20 mA

### Interface

USB

### Product Approvals

- CE
- UL
- FCC



### System Requirements

USB connection

MAC OS X 10.13 or higher

### Box Contents

- CHERRY KC 6000 SLIM FOR MAC
- Printed manual

### Dimensions (product)

approx. 440 x 130 x 15 mm / approx. 17.32 x 5.12 x .59 in

### Packaging Dimensions

approx. 453 x 170 x 33 mm / approx. 17.83 x 6.69 x 1.30 in

### Keyboard

- Key Technology: SX
- Service life, standard key: > 10 million key operations
- Inscription Technology: Laser
- Inscription Layout: Standard
- Number of Keys: Product dependant, see table "Models"

### Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 20

## Warranty

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below. For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

### Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase. CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty. Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.



## CHERRY KC 6000 SLIM FOR MAC

Corded Mac Keyboard

### Models

(possible country/layout versions, others available on request)

Product Name		Oder Number	EAN-Code	Layout (country or language)	Number of keys
	CHERRY KC 6000 SLIM FOR MAC	JK-1610US-1	4025112090158	US	104 + 6

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

JK-1610US-1