

SBB1002-1 *Proto Advantage*

Datasheet revision 1.0

www.Proto-Advantage.com

Solder Breadboard (10 row 2 column)

Product Highlights

Solder-in breadboard with 10 rows, 2 columns, and 2 power channels
120 holes in total
0.1" hole grid

Specifications

Dimensions:	27.94mm x 35.56mm (1.1" x 1.4")
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Hole size:	1.0mm (40 mils) diameter Holes accept 25 mil square wire wrap posts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[SBB1002-1](#)