



Datasheet revision 1.1

[www.Proto-Advantage.com](http://www.Proto-Advantage.com)

## Solder Breadboard (16 row 5 column)

### Product Highlights

Solder-in breadboard with 16 rows, 5 columns, and 2 power channels  
450 holes in total  
0.1" hole grid

### Specifications

Dimensions:	66.04mm x 60.96mm x 1.6mm (2.6" x 2.4" x 0.0625")
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Hole size:	1.0mm (40 mils) diameter Holes accept 25 mil square wire wrap posts
Diameter of 4 corner mounting holes:	3.2mm (125 mils)
Distance between mounting holes:	58.42mm x 53.34mm (2.3" x 2.1") (center-to-center)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[SBB1605-1](#)