



Datasheet revision 1.0

www.Proto-Advantage.com

Solder Breadboard (28 row 8 column)

Product Highlights

Solder-in breadboard with 28 rows, 8 columns, and 2 power channels
1200 holes in total
0.1" hole grid

Specifications

Dimensions:	104.14mm x 81.28mm (4.1" x 3.2")
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Hole size:	1.0mm (40 mils) diameter
	Holes accept 25 mil square wire wrap posts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[SBB2808-1](#)