





SPECIFICATIONS

Current Rating: 3 Amp
 Insulator Resistance: 1000 Megohms Min.
 Contact Resistance: 20 Milliohms Max.
 Dielectric Withstanding: AC 1000V/Minute
 Operating Temperature: -40°C To +105°C
 Contact: Brass, Gold Flash Over All
 Insulator: Polyester, PBT+30%GF, UL 94V-0



Recommended PCB Hole Layout

4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.

00548

SCALE

NONE

APPROVED BY

MEI

CHECKED BY

BECKY

DRAWING BY

HZF

REV.

A1

UNLESS OTHERWISE
 SPECIFIED
 TOLERANCES ARE


.X ±0.38

.XX ±0.25

ANG.

UNIT

mm



NO. REV.

A1 Modify Data

A0 NEW RELEASE

REVISIONS

BECKY

BECKY

CHK

09/30/2005

07/30/2004

DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[598](#)