





# SPECIFICATION

Current Rating:3 Amps  
Withstanding Voltage:500V AC  
Contact Resistance:20 Milliohms Max.  
Insulation Resistance:1000 Megaohms Min.  
Operation Temperature:-40°C~+105°C  
Housing:PA6T(UL94V-0),Black  
Contact:Brass,Gold Flash Over Nickel  
RoHS Compliant



Recommended P.C.B. Layout



**4UCON** 元化興業股份有限公司  
4UCON TECHNOLOGY INC.

DRAWING No.

00587

SCALE NONE

APPROVED BY

EMILY

CHECKED BY

HZF

DRAWING BY

YBL

REV.

A0

UNLESS OTHERWISE SPECIFIED

TOLERANCES ARE  
X. ±0.25 X.\* ±2°  
.X ±0.20 .X\* ±1.5°  
.XX ±0.15 .XX\* ±1°  
.XXX ±0.10 .XXX\* ±0.5°

UNIT mm



NO. REV.

NEW RELEASE

REVISIONS

CHK

DATE

04/08/2013

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[2222](#)