

P. C. B LAYOUT
BOTTOM VIEW

SPECIFICATION

1. Rating: DC 16V 3A
2. Contact resistance: 30 mΩ MAX.
3. Insulation resistance: 100 MΩ MIN.
4. Mechanical Life: 30,000 cycles.




MATERIALS

- CASE & HOUSING** - Glass filled Nylon 6/6, black.
ACTUATOR - Glass filled Nylon 6/6, gray.
CONTACT - Copper alloy, silver plated.
TERMINALS - Copper alloy, silver plated.
PIN - Brass, nickel plated.

PATENT NO. : M376887

▲ Packing: 1pcs/ per bag

▲ 包裝方式: 1PCS 一袋



SCHEMATIC

JCJ INTERNATIONAL CO.,LTD

SCALE(比例): 2:1

TOLERANCE (公差):
 0.00 mm ± 0.25mm
 0.0 mm ± 0.40mm
 ANGULAR: ± 5°
 FILE NAME : SJ0025

TITLE 圖名		DC POWER JACK WITH SWITCHES		SIZE 圖紙	A4
DWG NO. 圖號		SJ-004-P001		UNIT 單位	mm
REV. 版本	A	DATE 日期	JAN - 19 - 2018	SHEET 張數	1 of 1
CHECKED BY 審核	陳燈財	DRAWN BY 製圖		IRENE	

	符號	原尺寸	修改後尺寸	變更日期
1	(A)			
2	(B)			
3	(C)			
4	(D)			
5	(E)			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[3642](#)