


環保物料專用
RoHS compliant



Electrical Character:
100% Open/Short
Contact Resistance:3 Ohms Max.
Hi-Pot:200V AC/0.01S
Insulation Resistance: 10M Ohms Min.

Bill Of Material

6	TIE	TIE:Black	SET	1
5	Molding	Outer Over Moulding 35P PVC Color:Black	SET	1
4	Molding	internal mold PE Color:translucent	PCS	
3	CABLE	(10/0.10BC ID:0.75 HDPE White、Green)+(33/0.10BC ID:1.0mm PVC RED、BLACK) 75P PVC OD:3.5mm Jacket Color Black	PCS	
2	CONN	USB 3.1 C Type Male,Gold Flash pin,Solder Type,Natural Insulation,resistor 5.1KΩ	SET	1
1	CONN	Micro USB B Male front five back four, PBT Black Solder Type	SET	1
No.	Part	Material Name and Name	Unit	Qty

Wire Diagram

P1	Color	P2
1	Red VBSS	A1+B1+A12+B12
2	White D-	A7
3	GreEn D+	A6
5	Black GND	A4+B4+A9+B9
	resistor 5.1KΩ	A5



DESCRIPTION(内容):

USB TYPE C TO Micro-USB
B Type Male Cable Assembly

DRAWN(製圖):

Tom Liu

CHECKED(確認):

Jack Wu

APPROVAL(核准):

Kane He

GENERAL TOLERANCE

LINEAR ANGLES

X.: ±0.50 X°: ±5.0°

X.X: ±0.20 X.X°: ±3.0°

X.XX: ±0.15 X.XX°: ±2.0°

X.XXX: ±0.10 X.XXX°: ±1.0°

REV:

A/1

UNIT:

mm

SHEET:

1/2

REV

1

2

3

4

DESCRIPTION


ORIGINAL

DATE

Mar-28-2018

A4

SCALE(比例):
1:XX



THIRD ANGLE PROJECTION

PART NO:
(料 號)

CBUSB-CM-MCBM-305

DWG NO(圖號): KWRD180328-092

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[3879](#)