

TOLERANCE: ± 0.05
RECOMMENDED PCB LAYOUT
(TOP VIEW)

材质说明:

1. 塑胶主体 : 耐高温尼龙树脂, 加玻璃纤维30%.
2. 端子: 磷铜, T=0.25.
3. 固定焊片 : 黄铜合金, T=0.30 .

电镀要求:

1. 端子接触区域镀金 3u" min. ; 焊接区域镀锡80u" min. 镍底 50u" min.
2. 固定焊片表面镀锡80u" min.; 镍底50u" min. .

安规测试:


1. 产品符合 RoHS.

机械特性:

1. micro bit 与连接器插拔拔力 : 1Kg .
2. 插拔寿命: 1500次.


电气特性:

1. 额定电压: 250V AC.
2. 额定电流: 1AMP .
3. 接触阻抗 : 30 m Ω .
4. 绝缘阻抗 : 1000 M Ω , 500V DV.
5. 耐电压 : 500V 1Minute .




■ 表示焊接区域

REVISIONS				
LTR	DESCRIPTION	DATE	DWN	APVD
A	RELEASED	17\11\28	AW	WK



白色	MIC127-140-002
黑色	MIC127-140-001
塑胶颜色	PART NUMBER (料号)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU	2017\11\28	东莞市宇亮电子有限公司 DONG GUAN YU LIANG ELECTRONICS CO., LTD	
DIMENSIONS: mm		CHEK S. CHIEN	2017\11\28		
		APVD Abel	2017\11\28		
		PRODUCT SPEC —	SIZE A4	DRAWING No. C=YL-ED-0XXXX	
		WEIGHT —			
THIRD ANGLE PROJECTION		CUSTOMER DRAWING		SCALE 1 : 1	SHEET 1 OF 1
TOLERANCES UNLESS OTHERWISE SPECIFIED:					
0 PLC ± 0.50					
1 PLC ± 0.30					
2 PLC ± 0.20					
3 PLC ± 0.15					
4 PLC ± —					
ANGLES ± 3°					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[3887](#)