





REV.	ECN NO	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD





Notes:

1. Materials:

- 1.1 Housing: High temperature thermoplastic with g.f,UL94 V-0.
- 1.2 Contact: copper alloy,t=0.15mm.
- 1.3 Shell: copper alloy,t=0.30mm.

2. Specifications:

- 2.1. Current rating: 1 A Max.
- 2.2. Dielectric withstanding:voltage: 100 V(ac) for 1 min.
- 2.3. Contact resistance: 50 mW Max.
- 2.4. Insulation resistance: 100 MW Min.
- 2.5. Total mating force: 3.57 KgF Max.
- 2.6. Total unmating force: 1.0 KgF Min.0.81~2.05 KgF Min.after 10000 Insertion/extraction cycles
- 2.7. Temperature range: -30°C~+80°C



PART NO: 98-MB05PMXX-01		MATERIAL:	
MODEL NO:	FD098	FINSH:	
UNIT:	MM	SIZE:	A4
TOLERANCE UNSPECIFIED		DR:	
.x	±0.25	DWG NO:	
.xx	±0.10	CHK:	
.xxx	±0.05	APR:	
ANG.	±1°	SCALE:	1:1
		SHEET:	2008/12/18
		REV:	A

TITLE: MIRCO USB 5S B TYPE牛角型 D I P6.6/7.2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[4023](#)