


環保物料專用

RoHS compliant



SPECIFICATIONS

Current rating	:1A AC,DC
Voltage rating	:50V AC,DC
Temperature range	: -25°C ~ +85°C
Contact resistance	:20mΩMax
Insulation resistance	:100MΩMin
Withstanding voltage	:500V AC/minute
Pin Material	:Phosphor Bronze
Finished	:Tin-plated
Housing Material	:Nylon-6T,UL94 V-0
Color	:Black

Circuits	Dimensions	
	A	B
02	1.00	4.00
03	2.00	5.00
04	3.00	6.00
05	4.00	7.00
06	5.00	8.00
07	6.00	9.00
08	7.00	10.00
09	8.00	11.00
10	9.00	12.00
11	10.00	13.00
12	11.00	14.00
13	12.00	15.00
14	13.00	16.00
15	14.00	17.00
16	15.00	18.00
17	16.00	19.00
18	17.00	20.00
19	18.00	21.00
20	19.00	22.00



P.C.B Layout



A4

SCALE(比例):
1:XX



THIRD ANGLE PROJECTION

DESCRIPTION(内容):

1.00MM WAFER 180° SMT TYPE
REEL+CAP

PART NO:
(料 號) CCSH-W10-XX-BK-RC
DWG NO(圖號): KWRD190726-018

DRAWN(製圖):
Tom Liu

CHECKED(確認):
Jack Wu

APPROVAL(核准):
Kane He

GENERAL TOLERANCE

LINEAR ANGLES
X.: ±0.30 X°: ±5.0°
X.X: ±0.20 X.X°: ±3.0°

X.XX: ±0.15 X.XX°: ±2.0°
X.XXX: ±0.10 X.XXX°: ±1.0°

REV:

A/1

UNIT:
mm

SHEET:

1/1

REV:

1

2

3

4

DESCRIPTION

ORIGINAL

DATE

Jul-26-2019

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[4328](#)