

Silicone Cover Stranded-Core Wire – 25ft 26AWG – Gray

PRODUCT ID: 2519



DESCRIPTION

Silicone-sheathing wire is super-flexible and soft, and its also strong! Able to handle up to 200°C and up to 600V, it will do when PVC covered wire wimps out. We like this wire for being extremely supple and flexible, so it is great for wearables or projects where the wire-harness has to be able to deal with a lot of bending.

Comes with one 25ft spool of gray wire. The wire is 26AWG stranded with an outer diameter of 1.5mm.

Technical Details

Length: 25 feet / 7.6m

Outer Diameter: 1.5mm / 0.06"

Nominal Voltage: 600V

Temperature Range: -60°C ~ 200°C

OD Tolerance: ± 0.1 mm

Resistance: 123 Ω /Km

Current Handling Capability: ~3.5A (depends on length!)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[2519](#)