





環保物料專用
RoHS compliant



P.C.B. Hole Layout



SPECIFICATIONS

Current Rating	:3 Amp
Insulator Resistance	:5000 Megohms Min.
Contact Resistance	:20 m ohms max.
Dielectric Withstanding	:AC 1000 V
Operating Temperature	:-40°C ~ +105°C
Contact Material	:Phosphor Bronze
Insulator Material	:Polyester,UL 94V-0
Standard	:P.B.T
Finish	:Tin,Gold or Duplex Plated
Standard	:Gold Flash all over
Note:	
Duplex plating:	Gold Plated on contact area,Tin on Solder area

Ordering Information

F201-SGP-D055-XX

S:Straight
Type

G:Gold Flash
D:Gold/Tin Plated
T:Tin Plated

(04 TO 80
Contacts)



A4

SCALE(比例):
1:XX



THIRD ANGLE PROJECTION

DESCRIPTION(内容):

2.54mm Female Header 180°

PART NO:
(料 號) F201-SGP-D055-XX

DWG NO(圖號): KWRD180804-015

DRAWN(製圖):

Tom Liu

CHECKED(確認):

Jack Wu

APPROVAL(核准):

Kane He

GENERAL TOLERANCE

LINEAR ANGLES

X.: ± 0.30 X°: $\pm 5.0^\circ$

X.X: ± 0.20 X.X°: $\pm 3.0^\circ$

X.XX: ± 0.15 X.XX°: $\pm 2.0^\circ$

X.XXX: ± 0.10 X.XXX°: $\pm 1.0^\circ$

REV:

A/1

UNIT:

mm

SHEET:

1/1

REV

1

2

3

4

DESCRIPTION

ORIGINAL

Modify Terminal SPEC

DATE

Aug-04-2018

OCT-25-2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[4079](#)