

Customer Part:

Description

- Standard 7 x 5mm SMD crystal
- 4 pad (metal lid)
A ceramic package with a seam sealed metal lid, hermetically sealed. 4 pad device metal lid.
- Model 12SMX-B
- Model Issue number 14

Frequency Parameters

- Frequency 9.83040MHz
- Frequency Tolerance $\pm 30.00\text{ppm}$
- Frequency Stability $\pm 50.00\text{ppm}$
- Operating Temperature Range -20.00 to 70.00°C
- Overtone Order Fundamental
- Ageing $\pm 5\text{ppm}$ per year max

Electrical Parameters

- Load Capacitance 16.00pF
- Shunt Capacitance 7pF max
- Drive Level 100 μ W max
- ESR 80.00 Ω max

Environmental Parameters

- Storage Temperature Range: -40 to 125°C

Manufacturing Details

- RoHS Terminations NiAu
- RoHS Reflow Temp 260degC 10s

Compliance

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details

- Pack Style: Bulk Loose in bulk pack
Pack Size: 100
- *Alternative packing option available*



Outline (mm)



Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: 0800 1808 443

France: 0800 901 383
USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFX TAL032056Bulk](#)