


SWITCHING ADAPTER PART NUMBER CONFIGURATION

WALL MOUNT TYPE AC ADAPTER

TRXXXX	-	X	-	XX	X	XX
Model No.	AC Plug Type	DC Plug Type		OVP Option	DC Cable Length and Type	
A : USA 2 Pin		Straight/Inner+Outer-	Right Angle/Inner+Outer-	A: Without OVP Option E: With OVP Option	01: 720mm	
E : Europe 2 Pin					02:1220mm	
U : British 3 Pin		03:1800mm				
S : Australia 2 Pin		11:720mm with Ferrite Core				
		12:1220mm with Ferrite Core				
		13:1800mm with Ferrite Core				
		11 : 5.5 x 2.1 x 12mm	01 : 5.5 x 2.1 x 12mm			
		12 : 5.5 x 2.5 x 12mm	02 : 5.5 x 2.5 x 12mm			
		18 : 5.5 x 2.5 x 11mm	17 : 5.5 x 2.1 x 11mm			
		23 : 5.5 x 2.1 x 9.5mm	19 : 5.5 x 2.5 x 10.5mm			
		26 : 5.5 x 2.5 x 9.5mm	20 : 5.5 x 2.5 x 9mm			
		32 : 5.5 x 2.1 x 7.5mm	21 : 5.5 x 2.5 x 9.5mm			
		33 : 5.5 x 2.1 x 11.5mm	24 : 5.5 x 2.1 x 9.5mm			
		35 : 4.0 x 1.7 x 9.5mm	31 : 3.5 x 1.35 x 7.5mm			
		37 : 5.5 x 2.5 x 7.5mm	34 : 5.5 x 2.1 x 11.5mm			
		39 : 3.5 x 1.35 x 9mm	36 : 3.5 x 1.35 x 9mm			
		41 : 3.5 x 1.35 x 7.5mm	40 : 4.0 x 1.7 x 9.5mm			
		45 : 4.75 x 1.7 x 9.5mm	42 : 3.5 x 1.35 x 9.5mm			
		50 : 4.0 x 1.7 x 11mm	46 : 4.0 x 1.7 x 12mm			
			48 : 5 x 1.5 x 9.5mm			
			49 : 2.35 x 0.7 x 9.5mm			
		Straight/Inner-Outer+	Right Angle / Inner-Outer+			
						
		05 : 5.5 x 2.1 x 12mm	03 : 5.5 x 2.1 x 12mm			
		13 : 5.5 x 2.1 x 12mm	04 : 5.5 x 2.5 x 12mm			
		14 : 5.5 x 2.5 x 12mm	16 : 5.5 x 2.1 x 11mm			
		27 : 5.5 x 2.5 x 9.5mm	22 : 5.5 x 2.5 x 9.5mm			
			43 : 5.5 x 2.1 x 9.5mm			
			44 : 3.5 x 1.35 x 7.5mm			
			105 : 3.5 x 1.05 x 9.5mm			
			111 : 3.5 x 1.35 x 9.5mm			
			122 : 3.5 x 1.35 x 12mm			
			141 : 5.5 x 2.1 x 11mm			
			150 : 3.5 x 1.35 x 9mm			
			317 : 5.5 x 2.5 x 9mm			

DESK TOP TYPE AC ADAPTER

TRXXXXX -	XX	X	XX
Model No.	DC Plug Type	OVP Option	DC Cable Length and Type
	Straight/Inner+Outer-	A: Without OVP Option E : With OVP Option	01:720mm 02:1220mm 03:1800mm 11:720mm with Ferrite Core 12:1220mm with Ferrite Core 13:1800mm with Ferrite Core
			
11	: 5.5 x 2.1 x 12mm		
12	: 5.5 x 2.5 x 12mm		
18	: 5.5 x 2.5 x 11mm		
23	: 5.5 x 2.1 x 9.5mm		
26	: 5.5 x 2.5 x 9.5mm		
32	: 5.5 x 2.1 x 7.5mm		
33	: 5.5 x 2.1 x 11.5mm		
35	: 4.0 x 1.7 x 9.5mm		
37	: 5.5 x 2.5 x 7.5mm		
39	: 3.5 x 1.35 x 9mm		
41	: 3.5 x 1.35 x 7.5mm		
45	: 4.75 x 1.7 x 9.5mm		
50	: 4.0 x 1.7 x 11mm		
	Right Angle/Inner+Outer-		
			
01	: 5.5 x 2.1 x 12mm		
02	: 5.5 x 2.5 x 12mm		
17	: 5.5 x 2.1 x 11mm		
19	: 5.5 x 2.5 x 10.5mm		
20	: 5.5 x 2.5 x 9mm		
21	: 5.5 x 2.5 x 9.5mm		
24	: 5.5 x 2.1 x 9.5mm		
31	: 3.5 x 1.35 x 7.5mm		
34	: 5.5 x 2.1 x 11.5mm		
36	: 3.5 x 1.35 x 9mm		
40	: 4.0 x 1.7 x 9.5mm		
42	: 3.5 x 1.35 x 9.5mm		
46	: 4.0 x 1.7 x 12mm		
48	: 5 x 1.5 x 9.5mm		
49	: 2.35 x 0.7 x 9.5mm		
	Straight/Inner-Outer+		
			
05	: 5.5 x 2.1 x 12mm		
13	: 5.5 x 2.1 x 12mm		
14	: 5.5 x 2.5 x 12mm		
27	: 5.5 x 2.5 x 9.5mm		
	Right Angle/Inner-Outer+		
			
03	: 5.5 x 2.1 x 12mm		
04	: 5.5 x 2.5 x 12mm		
16	: 5.5 x 2.1 x 11mm		
22	: 5.5 x 2.5 x 9.5mm		
43	: 5.5 x 2.1 x 9.5mm		
44	: 3.5 x 1.35 x 7.5mm		

Cincon offers a wide variety of DC plugs for every customers.

Please contact your distributor or E-Mail sales@cincon.com.tw for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[TR70MB240-02E03](#)