

ACE-935AL

300 W PS/2 Type AT Power Supply



Specifications

Input Type	85 ~ 140 VAC, 170 ~ 270 VAC Auto Range					
Output Voltage	+3.3 V	+5 V	+12 V	-5 V	-12 V	+5 Vsb
		40 A (3A min)	8 A (0.1A min)	0.3 A	0.7 A	
Efficiency	68%					
Temperature	0°C ~ 50°C (Operating), -40°C ~ 75°C (Storage)					
MTBF (hrs)	100,000					
Output Connector	1 x P8+P9, 1 x Extra +5V (P10), 5 x HDD/CDROM, 2 x FDD					

Ordering Information

Part No.	Description
ACE-935AL-RS	300 W AC-DC PS/2 AT Power Supply, AC select switch

ACE-925AP-U

250 W PS/2 Type AT Power Supply



High reliability magnetic bearing cooling system features low noise, high operating temperature and longer MTBF



Specifications

Input	Voltage	90 ~ 265 VAC Full Range			
	Frequency	47 ~ 63 Hz			
Output	Voltage	+5 V	+12 V	-5 V	-12 V
	Max. load	22 A	11 A	0.5 A	0.7 A
General	MTBF	100,000 hours			
	Temperature	Operating: 0°C ~ 50°C Storage: -25°C ~ 70°C			
	Dimensions	140 x 150 x 86 (mm)			
	Output Connector	1 x P8+P9, 4 x HDD/CDROM, 2 x FDD, 2 x SATA			

Ordering Information

Part No.	Description
ACE-925AP-U-RS	250 W AC-DC PS/2 AT Power Supply, with PFC

ACE-925A

200 W PS/2 Type AT Power Supply



Specifications

Input Type	85 ~ 265VAC Full Range					
Output Voltage	+3.3 V	+5 V	+12 V	-5 V	-12 V	+5 Vsb
		22 A (1A min)	7 A (0.1A min)	0.5 A	0.7 A	
Efficiency	68%					
Temperature	0°C ~ 50°C (Operating), -40°C ~ 75°C (Storage)					
MTBF (hrs)	130,000					
Output Connector	1 x P8+P9, 5 x HDD/CDROM, 2 x FDD					

Ordering Information

Part No.	Description
ACE-925A-RS	200 W AC-DC PS/2 AT Power Supply

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[ACE-935AL-RS](#) [ACE-925AP-U-RS](#) [ACE-925A-RS](#)