


IMB-Q870-i2


microATX motherboard supports 22nm LGA1150 Intel® Core™ i7/i5/i3, Pentium® and Celeron® CPU per Intel® Q87, DDR3, HDMI, VGA, iDP, USB 3.0, SATA 6Gb/s, Six Serial Ports, iRIS-2400



New and More Powerful Graphics

New

2nd Generation Intel® Core Processor (Sandy Bridge)	3rd Generation Intel® Core Processor (Ivy Bridge)	4th Generation Intel® Core Processor (Haswell)	
Intel® HD Graphics 3000 series	Intel® HD Graphics 4000 series	GT3-Intel® HD Graphics 5000 series	Core i7
Intel® HD Graphics 2000 series	Intel® HD Graphics 2500 series	GT2-Intel® HD Graphics 4000 series	Core i5/ Core i3
Intel® HD Graphicsseries	Intel® HD Graphicsseries	GT1-Intel® HD Graphics series	Celeron/ Pentium



Specifications

- ◆ CPU
LGA1150 Intel® 4th generation Core™ i7/i5/i3, Pentium® or Celeron® processor supported
- ◆ System Chipset
Intel® Q87
- ◆ Memory
Four 240-pin 1600/1333MHz dual-channel DDR3 & DDR3L SDRAM unbuffered DIMMs support up to 32GB
- ◆ BIOS
UEFI BIOS
- ◆ Ethernet
LAN1: Intel® I217LM with Intel® AMT 9.0 support
LAN2: Intel® I210-AT PCIe controller with NCSI support
- ◆ Graphics Engine
Intel® HD Graphics Gen 7.5 supports DX11.1 and OpenCL 1.2, OpenGL 4.3
Full MPEG2, VC1, AVC Decode
- ◆ Display Output
VGA (up to 1920x1200 @ 60 Hz)
DVI-D (up to 2560x1600 @ 60 Hz)
HDMI (up to 2560x1600 @ 60 Hz)
iDP interface for HDMI, LVDS, VGA, DVI, DP (up to 3840x2160 @60 Hz)
- ◆ Super I/O
Fintek F81866
- ◆ Audio
Realtek ALC662 HD Audio codec (Line-in, Line-out, Mic)
- ◆ I/O Interface
 - 5 x RS-232
 - 1 x RS-422/485
 - 1 x 6-pin wafer for PS/2 KB/MS
 - 1 x PS/2 KB/MS connector (rear I/O)
 - 4 x USB 3.0 (2 on rear, 2 by pin header)
 - 8 x USB 2.0 (4 on rear, 4 by pin header)
 - 4 x SATA 6Gb/s (RAID 0/1/5/10 support)
- ◆ Front Audio
1 x 10-pin (2x5) header
- ◆ Front Panel
1 x Front panel (Power LED, HDD LED, Speaker, Power Button, Reset Button)
- ◆ LAN LED
2 x 2-pin headers for LAN1 Link LED, LAN2 Link LED
- ◆ TPM
1 x TPM connector (2x10 pin)
- ◆ SMBus
1 x 4-pin (1x4) wafer
- ◆ I2C
1 x 4-pin (1x4) wafer
- ◆ iRIS Remote Management Module
1 x iRIS-2400 slot
- ◆ Expansion
 - 1 x PCIe x16 slot (Gen 3)
 - 1 x PCIe x4 slot
 - 1 x PCIe x1 slot
 - 1 x PCI slot
- ◆ Watchdog Timer
Software programmable, support 1~255 sec. system reset
- ◆ Digital I/O
8-bit digital I/O (4-bit input, 4-bit output)
- ◆ Fan Connector
1 x 4-pin CPU fan connector
2 x 3-pin system fan connector
- ◆ Power Supply: ATX power supply
- ◆ Power Consumption
3.3V@0.53A, 5V@4.96A, 12V@0.12A, Vcore_12V@3.95A, 5VSB@0.18A
(Intel® Core™ i7-4770K 3.90 GHz CPU with 16GB (4x4GB) 1333MHz DDR3 memory)
- ◆ Operating Temperature: -20°C ~ 60°C
- ◆ Storage Temperature: -30°C ~ 70°C
- ◆ Operating Humidity: 5% ~ 95%, non-condensing
- ◆ Dimensions: 244mm x 244mm
- ◆ Weight: GW:1200g, NW: 700g

Features

1. LGA1150 Intel® 4th generation Core™ i7/i5/i3, Pentium® or Celeron® processor supported
2. Dual-channel DDR3 1600/1333MHz supported
3. Intel® PCIe GbE with Intel® AMT 9.0 support
4. Support triple display via HDMI, DVI, VGA and iDP
5. Support PCI Express generation 3.0 at 8GT/s I/O bandwidth
6. USB 3.0 and SATA 6Gb/s supported
7. IEI jumper-less function
8. IEI One Key Recovery solution allows you to create rapid OS backup and recovery
9. Support IPMI 2.0 via iRIS-2400 module

Packing List

1 x IMB-Q870-i2 single board computer	
2 x SATA cable (P/N: 32000-062800-RS)	1 x Utility CD
1 x I/O shielding (P/N: 45014-0046C0-00-RS)	1 x QIG

Ordering Information

Part No.	Description
IMB-Q870-i2-R10	microATX motherboard supports 22nm LGA1150 Intel® Core™ i7/i5/i3/Pentium® and Celeron® CPU per Intel® Q87, DDR3, HDMI, DVI-D, VGA, DP, Dual Intel® PCIe GbE, USB 3.0, Audio, SATA 6Gb/s, Six Serial Ports, iRIS-2400 and RoHS
iRIS-2400-R10	IPMI 2.0 adapter card with AST2400 BMC chip for DDR3 SO-DIMM socket interface
19800-003100-300-RS	Dual-port USB 2.0 cable with bracket
19800-010500-200-RS	USB 3.0 cable 457mm with bracket
32205-003800-300-RS	RS-422/485 cable, 200mm
32205-001203-200-RS	RS-232 cable, 40-pin to four DB-9
32102-000100-200-RS	SATA power cable, MOLEX 5264-4P to SATA15P
19800-000075-RS	PS/2 KB/MS Y-cable with bracket, 220mm
19800-000049-RS	LPT cable
CF-1156A-RS-R11	High performance LGA1155/LGA1156 cooler kit, 1U chassis compatible, 73W
CF-1156E-R11	High performance LGA1155/LGA1156 cooler kit, 95W
DP-LVDS-R10	DisplayPort to 24-bit dual-channel LVDS converter board (for IEI iDP connector)
DP-HDMI-R10	DisplayPort to HDMI converter board (for IEI iDP connector)
DP-DVI-R10	DisplayPort to DVI-D converter board (for IEI iDP connector)
DP-VGA-R10	DisplayPort to VGA converter board (for IEI iDP connector)
DP-DP-R10	DisplayPort to DisplayPort converter board (for IEI iDP connector)
TPM-IN01-R11	20-pin Infineon TPM module, software management tool, firmware V3.17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[IMB-Q870-i2-R10](#)