



PCIE-Q870-i2

Full-size PICMG 1.3 CPU card supports LGA1150 Intel® Core™ i7/i5/i3, Pentium® and Celeron® CPU per Intel® Q87, DDR3, VGA, iDP, Dual PCIe GbE, SATA 6Gb/s, mSATA, PCIe Mini, RS-232, Audio, iRIS-2400 and RoHS



New

iRIS-2400 Key Features


- IPMI 2.0 Based Management
- Cross OS Platform Support
- Hardware Health Monitor
- Event Log
- KVM over IP
- Notifications
- Virture Media Support
- Remote Power Control
- User Management
- Serial over LAN



Enhance component protection
Prevent the damage of bottom size components

Specifications

- ◆ CPU
LGA1150 Intel® 4th generation Core™ i7/i5/i3, Pentium® or Celeron® processor supported
- ◆ System Chipset
Intel® Q87
- ◆ Memory
Four 240-pin 1600/1333MHz dual-channel DDR3 & DDR3L SDRAM unbuffered DIMMs support up to 32GB
- ◆ BIOS
UEFI BIOS
- ◆ Graphics Engine
Intel® HD Graphics Gen 7.5 supports DX11.1 and OpenCL 1.2, OpenGL 3.2 Full MPEG2, VC1, AVC Decode
- ◆ Display Output
VGA (up to 1920x1200 @ 60 Hz)
iDP interface for HDMI, LVDS, VGA, DVI, DP (up to 3840x2160 @60 Hz)
- ◆ Ethernet
LAN1: Intel® I217LM with Intel® AMT 9.0 support
LAN2: Intel® I210-AT PCIe controller with NCSI support
- ◆ Super I/O
Fintek F81866
- ◆ I/O Interface
 - 1 x 6-pin wafer for KB/MS
 - 1 x LPT
 - 1 x RS-422/485
 - 4 x RS-232
 - 1 x mSATA (colay SATA port 6) (support SATA 6GB/s signal only)
 - 4 x USB 3.0 (2 by rear IO, 2 by pin header)
 - 6 x SATA 6GB/s (RAID 0, 1, 5, 10 supported)
 - 8 x USB 2.0 (4 by pin header, 4 by backplane pin header)
- ◆ Front Panel
1 x Front panel (Power LED, HDD LED, Speaker, Power Button, Reset Button)
- ◆ LAN LED
2 x 2-pin headers for LAN1 Link LED, LAN2 Link LED
- ◆ Audio
Supported by IEI AC-KIT-892HD Audio Kit
- ◆ TPM
1 x TPM connector (2x10 pin)
- ◆ SMBus
1 x 4-pin wafer
- ◆ I2C
1 x 4-pin wafer
- ◆ Infrared Interface
1 x 5-pin header
- ◆ iRIS Remote Management Module
1 x iRIS-2400 slot
- ◆ Expansion
PCIe signal and PCI signal via golden finger
PCI signal by ITE 8892 (PCIe to PCI bridge)
1 x Full-size PCIe Mini card slot (colay mSATA)
- ◆ Watchdog Timer
Software programmable, support 1~255 sec. system reset
- ◆ Digital I/O
8-bit digital I/O (4-bit input, 4-bit output)
- ◆ Fan Connector
1 x 3-pin fan connector (system fan)
1 x 4-pin smart fan connector (CPU fan)
- ◆ Power Supply
5V/12V, AT/ATX support
- ◆ Power Consumption
5V@3.55A, 12V@0.37A, Vcore_12V@7.61A, 3.3V@1.55A, 5VSB@0.13A (Intel® Core™ i7-4770K 3.90 GHz CPU with 16GB (4x4GB) 1333MHz DDR3 memory)
- ◆ Operating Temperature
-20°C ~ 60°C
- ◆ Storage Temperature
-30°C ~ 70°C
- ◆ Operating Humidity
10% ~ 95%, non-condensing
- ◆ Dimensions
338 mm x 126 mm
- ◆ Weight
GW 1200g / NW: 420g



Features

- PICMG 1.3 full-size graphic grade solution
- LGA1150 Intel® 4th generation Core™ i7/i5/i3, Pentium® or Celeron® processor supported
- Four 240-pin 1600/1333MHz dual-channel DDR3 DIMMs support up to 32GB memory
- Supports dual independent display by VGA & iDP interface
- Supports PCIe Mini devices and mSATA via PCIe Mini socket
- Intel® PCIe GbE with Intel® AMT 9.0 support
- Supports RAID function via SATA 6Gb/s
- TPM V1.2 hardware security function supported by TPM module
- Stiffener bars
- IEI jumper-less function
- Support IPMI 2.0 via iRIS-2400 module

Packing List

1 x PCIE-Q870-i2 single board computer	
1 x Dual RS-232 cable (P/N: 19800-000051-RS)	
1 x USB 2.0 cable (P/N: 19800-003100-300-RS)	1 x QIG (Quick Installation Guide)
2 x SATA cable (P/N: 32000-062800-RS)	1 x Utility CD

Ordering Information

Part No.	Description
PCIE-Q870-i2-R10	Full-size PICMG 1.3 CPU card supports LGA1150 Intel® Core™ i7/i5/i3, Pentium® and Celeron® CPU per Intel® Q87, DDR3, VGA, iDP, Dual Intel® PCIe GbE, SATA 6Gb/s, mSATA, RS-232, PCIe Mini, Audio, iRIS-2400 and RoHS
iRIS-2400-R10	IPMI 2.0 adapter card with AST2400 BMC chip for DDR3 SO-DIMM socket interface
19800-000049-RS	LPT cable
19800-000075-RS	KB/MS cable with bracket
19800-010500-200-RS	USB 3.0 cable 457mm with bracket
32102-000100-200-RS	SATA power cable, MOLEX 5264-4P to SATA15P
32205-003800-300-RS	RS-422/485 cable, 200mm
AC-KIT-892HD-R10	7.1 channel HD Audio kit with Realtek ALC892 support dual audio streams
CF-1150SB-R11	Special cooler kit for LGA1150, high-performance compatible, 65W
CF-1150SC-R20	Special cooler kit for LGA115X, 1U chassis compatible, 65W, copper
CF-1150SE-R10	Special cooler kit for LGA115X, high-performance compatible, 95W, cooper
CF-1150SF-R10	Special cooler kit for LGA115X Intel® CPU, 107x70x35, 54W
DP-DP-R10	DisplayPort to DisplayPort converter board (for IEI iDP connector)
DP-DVI-R10	DisplayPort to DVI-D converter board (for IEI iDP connector)
DP-HDMI-R10	DisplayPort to HDMI converter board (for IEI iDP connector)
DP-LVDS-R10	DisplayPort to LVDS converter board (for IEI iDP connector)
DP-VGA-R10	DisplayPort to VGA converter board (for IEI iDP connector)
TPM-IN01-R11	20-pin Infineon TPM module, software management tool, firmware V3.17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[PCIE-Q870-i2-R10](#)