


RP325


3-PHASE **DELTA** DUAL STAGE POWER LINE FILTER

FEATURES

- » Rated currents include **15A, 30A, 50A, 80A, 100A, 150A, 200A, and 300A**
- » Dual Stage Line Filter
- » Available with **W** (wires), **S** (studs) and **C** (connectors) option
- » Agency Approved to UL1283 / 60929, CSA C22.2, EN 60939
- » Y-cap value can be adjusted to fit specification



ELECTRICAL SCHEMATIC



SPECIFICATIONS

OPERATING FREQUENCY	50/60Hz
USABLE FREQUENCY	DC - 400 Hz
MAX. OPERATING VOLTAGE*	480V +10%
AMBIENT TEMPERATURE	-25 TO 50°C
CLIMATIC CATEGORY	25/100/21
TERMINALS (-T)	WIRE LEADS
	STUDS 15-50A(M5),
	80-100A(M6),
	150-200A(M10),
	300A(M12)
	CONNECTORS
	4.7-25.0 (2.1-11.3)
TYP. WEIGHT, LBS (KG)	

TYPICAL LEAKAGE CURRENT

@ 480 VAC 60 Hz	0 - 20.0 mA Max.
-----------------	------------------

HIPOT RATINGS

LINE TO GROUND	3500 VDC
----------------	----------

TYPICAL APPLICATIONS

- ✓ High Power Rectifiers
- ✓ Uninterrupted Power Supplies
- ✓ Inverters
- ✓ Industrial Automation Equipment
- ✓ Medical Devices
- ✓ General Purpose 3-Phase Filter Needs

HOW TO ORDER

RP325- X - Y - Z

- Z = TERMINAL (-T)
- Y = Y-CAP, NF
- X = RATED CURRENT
- RP350 = FILTER SERIES

NOTE: USE ANY COMBINATION OF -X (AMPS) WITH ANY -Y RATINGS

E.G. **RP325-50-1000-S** (50AMPS WITH 1000 NF YCAP)

For **X**, **Y** and **Z** options see product specification table.

RP325

3-PHASE **DELTA** DUAL STAGE POWER LINE FILTER

MODEL NO.	RATED CURRENT, A @ 40° C	Y-CAP, nF	LEAKAGE CURRENT mA, @ 480V AC/60 Hz	TERMINAL OPTIONS			MAX. DIMENSIONS" (MM)		
				(W) INPUT/OUTPUT	(S) INPUT/OUTPUT	(C) INPUT/OUTPUT	WIDTH	(LENGTH)	HEIGHT
RP325-15-0-S	15	0	-		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-15-0-W	15	0	-	✓			*	*	*
RP325-15-10-S	15	10	0.10		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-15-10-W	15	10	0.10	✓			*	*	*
RP325-15-100-S	15	100	1.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-15-100-W	15	100	1.00	✓			*	*	*
RP325-15-1000-S	15	1000	10.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-15-1000-W	15	1000	10.00	✓			*	*	*
RP325-15-2000-S	15	2000	20.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-15-2000-W	15	2000	20.00	✓			*	*	*
RP325-30-0-C	30	0	-			✓	*	*	*
RP325-30-0-S	30	0	-		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-30-0-W	30	0	-	✓			*	*	*
RP325-30-10-C	30	10	0.10			✓	*	*	*
RP325-30-10-S	30	10	0.10		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-30-10-W	30	10	0.10	✓			*	*	*
RP325-30-100-C	30	100	1.00			✓	*	*	*
RP325-30-100-S	30	100	1.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-30-100-W	30	100	1.00	✓			*	*	*
RP325-30-1000-C	30	1000	10.00			✓	*	*	*
RP325-30-1000-S	30	1000	10.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-30-1000-W	30	1000	10.00	✓			*	*	*
RP325-30-2000-C	30	2000	20.00			✓	*	*	*
RP325-30-2000-S	30	2000	20.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-30-2000-W	30	2000	20.00	✓			*	*	*
RP325-50-0-C	50	0	-			✓	*	*	*
RP325-50-0-S	50	0	-		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-50-0-W	50	0	-	✓			*	*	*
RP325-50-10-C	50	10	0.10			✓	*	*	*
RP325-50-10-S	50	10	0.10		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-50-10-W	50	10	0.10	✓			*	*	*
RP325-50-100-C	50	100	1.00			✓	*	*	*
RP325-50-100-S	50	100	1.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-50-100-W	50	100	1.00	✓			*	*	*

ADDITIONAL MODEL NO. >>

RP325

3-PHASE **DELTA** DUAL STAGE POWER LINE FILTER

MODEL NO.	RATED CURRENT, A @ 40° C	Y-CAP, nF	LEAKAGE CURRENT mA, @ 480V AC/60 Hz	TERMINAL OPTIONS			MAX. DIMENSIONS" (MM)		
				(W) INPUT/OUTPUT	(S) INPUT/OUTPUT	(C) INPUT/OUTPUT	WIDTH	(LENGTH)	HEIGHT
RP325-50-1000-C	50	1000	10.00			✓	*	*	*
RP325-50-1000-S	50	1000	10.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-50-1000-W	50	1000	10.00	✓			*	*	*
RP325-50-2000-C	50	2000	20.00			✓	*	*	*
RP325-50-2000-S	50	2000	20.00		✓		3.50"(89)	10.00"(254)	2.75"(70)
RP325-50-2000-W	50	2000	20.00	✓			*	*	*
RP325-80-0-C	80	0	-			✓	*	*	*
RP325-80-0-S	80	0	-		✓		4.00"(102)	12.00"(305)	3.25"(83)
RP325-80-0-W	80	0	-	✓			*	*	*
RP325-80-10-C	80	10	0.10			✓	*	*	*
RP325-80-10-S	80	10	0.10		✓		4.00"(102)	12.00"(305)	3.25"(83)
RP325-80-10-W	80	10	0.10	✓			*	*	*
RP325-80-100-C	80	100	1.00			✓	*	*	*
RP325-80-100-S	80	100	1.00		✓		4.00"(102)	12.00"(305)	3.25"(83)
RP325-80-100-W	80	100	1.00	✓			*	*	*
RP325-80-1000-C	80	1000	10.00			✓	*	*	*
RP325-80-1000-S	80	1000	10.00		✓		4.00"(102)	12.00"(305)	3.25"(83)
RP325-80-1000-W	80	1000	10.00	✓			*	*	*
RP325-80-2000-C	80	2000	20.00			✓	*	*	*
RP325-80-2000-S	80	2000	20.00		✓		4.00"(102)	12.00"(305)	3.25"(83)
RP325-80-2000-W	80	2000	20.00	✓			*	*	*
RP325-100-0-C	100	0	-			✓	*	*	*
RP325-100-0-S	100	0	-		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-100-0-W	100	0	-	✓			*	*	*
RP325-100-10-C	100	10	0.10			✓	*	*	*
RP325-100-10-S	100	10	0.10		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-100-10-W	100	10	0.10	✓			*	*	*
RP325-100-100-C	100	100	1.00			✓	*	*	*
RP325-100-100-S	100	100	1.00		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-100-100-W	100	100	1.00	✓			*	*	*
RP325-100-1000-C	100	1000	10.00			✓	*	*	*
RP325-100-1000-S	100	1000	10.00		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-100-1000-W	100	1000	10.00	✓			*	*	*
RP325-100-2000-C	100	2000	20.00			✓	*	*	*

ADDITIONAL MODEL NO. >>

RP325

3-PHASE **DELTA** DUAL STAGE POWER LINE FILTER

MODEL NO.	RATED CURRENT, A @ 40° C	Y-CAP, nF	LEAKAGE CURRENT mA, @ 480V AC/60 Hz	TERMINAL OPTIONS			MAX. DIMENSIONS" (MM)		
				(W) INPUT/OUTPUT	(S) INPUT/OUTPUT	(C) INPUT/OUTPUT	WIDTH	(LENGTH)	HEIGHT
RP325-100-2000-S	100	2000	20.00		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-100-2000-W	100	2000	20.00	✓			*	*	*
RP325-150-0-C	150	0	-			✓	*	*	*
RP325-150-0-S	150	0	-		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-150-0-W	150	0	-	✓			*	*	*
RP325-150-10-C	150	10	0.10			✓	*	*	*
RP325-150-10-S	150	10	0.10		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-150-10-W	150	10	0.10	✓			*	*	*
RP325-150-100-C	150	100	1.00			✓	*	*	*
RP325-150-100-S	150	100	1.00		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-150-100-W	150	100	1.00	✓			*	*	*
RP325-150-1000-C	150	1000	10.00			✓	*	*	*
RP325-150-1000-S	150	1000	10.00		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-150-1000-W	150	1000	10.00	✓			*	*	*
RP325-150-2000-C	150	2000	20.00			✓	*	*	*
RP325-150-2000-S	150	2000	20.00		✓		6.40"(163)	15.75"(400)	5.68"(144)
RP325-150-2000-W	150	2000	20.00	✓			*	*	*
RP325-200-0-C	200	0	-			✓	*	*	*
RP325-200-0-S	200	0	-		✓		6.61"(168)	15.75"(400)	4.49"(114)
RP325-200-0-W	200	0	-	✓			*	*	*
RP325-200-10-C	200	10	0.10			✓	*	*	*
RP325-200-10-S	200	10	0.10		✓		6.61"(168)	15.75"(400)	4.49"(114)
RP325-200-10-W	200	10	0.10	✓			*	*	*
RP325-200-100-C	200	100	1.00			✓	*	*	*
RP325-200-100-S	200	100	1.00		✓		6.61"(168)	15.75"(400)	4.49"(114)
RP325-200-100-W	200	100	1.00	✓			*	*	*
RP325-200-1000-C	200	1000	10.00			✓	*	*	*
RP325-200-1000-S	200	1000	10.00		✓		6.61"(168)	15.75"(400)	4.49"(114)
RP325-200-1000-W	200	1000	10.00	✓			*	*	*
RP325-200-2000-C	200	2000	20.00			✓	*	*	*
RP325-200-2000-S	200	2000	20.00		✓		6.61"(168)	15.75"(400)	4.49"(114)
RP325-200-2000-W	200	2000	20.00	✓			*	*	*
RP325-300-0-S	300	0	-		✓		7.00"(178)	20.01"(508)	5.00"(127)
RP325-300-10-S	300	10	0.10		✓		7.00"(178)	20.01"(508)	5.00"(127)

ADDITIONAL MODEL NO. >>


RP325

3-PHASE **DELTA** DUAL STAGE POWER LINE FILTER

MODEL NO.	RATED CURRENT, A @ 40° C	Y-CAP, nF	LEAKAGE CURRENT mA, @ 480V AC/60 Hz	TERMINAL OPTIONS			MAX. DIMENSIONS" (MM)		
				(W) INPUT/OUTPUT	(S) INPUT/OUTPUT	(C) INPUT/OUTPUT	WIDTH	(LENGTH)	HEIGHT
RP325-300-100-S	300	100	1.00		✓		7.00"(178)	20.01"(508)	5.00"(127)
RP325-300-1000-S	300	1000	10.00		✓		7.00"(178)	20.01"(508)	5.00"(127)
RP325-300-2000-S	300	2000	20.00		✓		7.00"(178)	20.01"(508)	5.00"(127)

*Contact factory for dimensions.

RP325 MECHANICAL OUTLINES (MM)



SERIES	(A)	(B)	(C)	(D)	(E)	(F)	(G)	(H)	(I)	(J)	(K)	(L)	(M)	(N)	(O)	(P)	(Q)
STUDS (15/30/50A)	10.00" (254)	3.50" (89)	2.75" (70)	9.00" (229)	8.00" (203)	3.50" (89)	1.90" (48)	0.80" (20)	2.70" (69)	2.26" (57)	0.75" (19)	Ø, 0.29"x6.4, 4x Ø, 7.6x6.4, 4x	STUD, GND, M5	STUD, M5, 6x	0.50" (13)	2.50" (64)	0.50" (13)
STUDS (80A)	12.00" (305)	4.00" (102)	3.25" (83)	11.00" (279)	10.00" (254)	4.00" (102)	2.00" (51)	1.00" (25)	3.00" (76)	2.25" (57)	1.00" (25)	Ø, 0.25"x7.6, 4x Ø, 6.4x7.6, 4x	STUD, GND, M6	STUD, M6, 6x	0.50" (13)	3.00" (76)	0.50" (13)
STUDS (100/150A)	15.75" (400)	6.40" (163)	5.68" (144)	14.70" (373)	13.00" (330)	6.60" (168)	3.30" (84)	1.65" (42)	4.95" (126)	3.50" (89)	1.00" (25)	Ø, 0.29"x15.20, 4x Ø, 7.62x15.20, 4x	STUD, GND, M6	STUD, M6, 6x	0.53" (13)	5.12" (130)	0.74" (19)
STUDS (200A)	15.75" (400)	6.61" (168)	4.49" (114)	14.70" (373)	12.99" (330)	6.61" (168)	3.31" (84)	1.65" (42)	4.96" (126)	3.50" (89)	1.00" (25)	Ø, 0.29"x15.20, 4x Ø, 7.62x15.20, 4x	STUD, GND, M10	STUD, M10, 6x	0.75" (19)	5.12" (130)	0.52" (13)
STUDS (300A)	20.01" (508)	7.00" (178)	5.00" (127)	19.01" (483)	18.00" (457)	7.00" (178)	3.50" (89)	1.75" (45)	5.25" (133)	4.00" (102)	1.00" (25)	Ø, 0.59"x7.6, 4x Ø 15.2x7.6, 4x	STUD, GND, M10	STUD, M12, 6x	0.50" (13)	6.00" (152)	0.50" (13)

TYPICAL TOLERANCE: +/-0.02" (0.50MM)

RP325

3-PHASE **DELTA** DUAL STAGE POWER LINE FILTER

TYPICAL INSERTION LOSS, dB (50/50 Ohm)

Amps	Freq (MHz)	0.15	0.5	1.0	10	30
15	CM (dB)	65	75	75	58	40
	DM (dB)	65	75	75	75	70
30	CM (dB)	65	75	75	58	40
	DM (dB)	65	75	75	75	70
50	CM (dB)	58	70	70	58	40
	DM (dB)	60	70	75	70	60
80	CM (dB)	54	65	65	55	40
	DM (dB)	55	60	60	50	38
100	CM (dB)	70	75	75	58	30
	DM (dB)	55	70	70	60	30
150	CM (dB)	65	70	70	55	30
	DM (dB)	50	65	70	60	30
200	CM (dB)	60	65	60	50	35
	DM (dB)	50	65	70	60	30
300	CM (dB)	60	65	60	48	40
	DM (dB)	55	55	55	50	30

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[RP325-150-2000-S](#) [RP325-150-100-S](#) [RP325-80-100-S](#) [RP325-50-0-S](#) [RP325-50-10-S](#) [RP325-300-100-S](#)