


RPM8500


MIL/COTS 3-PHASE **DELTA** EMI POWER LINE FILTER

FEATURES

- » Rated currents include **5A, 10A, 20A, 30A, 50A, 70A, 125A and 150A**
- » Dual Stage Line Filter
- » Available with **S** (studs)
- » Agency Approved to RoHS
- » Y-cap value can be adjusted to fit specification



ELECTRICAL SCHEMATIC



SPECIFICATIONS

OPERATING FREQUENCY	50/60/400 Hz
MAX. OPERATING VOLTAGE	480 VAC +10%
AMBIENT TEMPERATURE	-40 TO 70°C
CLIMATIC CATEGORY	25/100/21
TERMINALS (-T)	STUDS: 5-50A (M5), 70A (M6), 125-150A (M10)

TYP. WEIGHT, LBS (KG)	2.8 - 16(1.27 - 7.25)
-----------------------	-----------------------

TYPICAL LEAKAGE CURRENT

@ 480 VAC 60 Hz	0 - 3.50 mA Max.
-----------------	------------------

HIPOT RATINGS

LINE TO GROUND	1800 VDC
----------------	----------

TYPICAL APPLICATIONS

- ✓ Mil-461/ DO-160

NOTE:

- ✓ Call for other termination types (e.g. Circular Mil-Connector, etc.)

HOW TO ORDER

RPM8500 - Y - Z

Z = TERMINAL (-T)
X = RATED CURRENT

RPM8500=FILTER SERIES

NOTE: USE ANY COMBINATION OF -X (AMPS) WITH ANY -Y RATINGS

E.G. **RPM8500-10-S** (10 AMPS)


For **X** and **Y** options see product specification table.

RPM8500

MIL/COTS 3-PHASE **DELTA** EMI POWER LINE FILTER

MODEL NO.	RATED CURRENT, A @ 40° C	LEAKAGE CURRENT, mA @ 480V AC, 60 Hz	TERMINAL OPTIONS			MAX. DIMENSIONS" (MM)		
			(QD) INPUT/ OUTPUT	(W) INPUT/ OUTPUT	(S) INPUT/ OUTPUT	WIDTH	(LENGTH)	HEIGHT
RPM8500-5-S	5	3.50			✓	4.25"(108)	6.06"(154)	2.25"(57)
RPM8500-10-S	10	3.50			✓	4.25"(108)	6.06"(154)	2.25"(57)
RPM8500-20-S	20	3.50			✓	3.50"(89)	10.00"(254)	2.75"(70)
RPM8500-30-S	30	3.50			✓	3.50"(89)	10.00"(254)	2.75"(70)
RPM8500-50-S	50	3.50			✓	4.00"(102)	12.00"(305)	3.25"(83)
RPM8500-70-S	70	3.50			✓	4.00"(102)	12.00"(305)	3.25"(83)
RPM8500-125-S	125	3.50			✓	6.40"(163)	15.99"(406)	4.50"(114)
RPM8500-150-S	150	3.50			✓	6.40"(163)	15.99"(406)	4.50"(114)

RPM8500 MECHANICAL OUTLINES (MM)



SERIES	(A)	B	C	D	E	F	G	H	I	J	K	L	M	N	O	P	Q
STUDS (5/10A)	6.06" (154)	4.25" (108)	2.25" (57)	3.50" (89)	4.25" (108)	4.25" (108)	1.85" (47)	0.75" (19)	2.13" (54)	1.80" (46)	0.75" (19)	Ø 0.20"x0.44",4x (Ø 5.1x11.2, 4x)	STUD M5, 6x	STUD GND M5	0.38" (10)	5.00" (127)	0.38" (10)
STUDS (20/30A)	10.00" (254)	3.50" (89)	2.75" (70)	2.50" (64)	8.00" (203)	3.50" (89)	1.90" (48)	0.80" (20)	1.75" (45)	2.05" (52)	0.75" (19)	Ø 0.29"x0.25",4x (Ø 7.6x6.4, 4x)	STUD, M5, 6x	STUD, GND, M5	0.50" (13)	9.00" (229)	0.50" (13)
STUDS (50/70A)	12.00" (305)	4.00" (102)	3.25" (83)	3.00" (76)	10.00" (254)	4.00" (102)	2.00" (51)	1.00" (25)	2.00" (51)	2.25" (57)	1.00" (25)	Ø 0.29"x0.25",4x (Ø 7.6x6.4, 4x)	STUD, M6, 6x	STUD, GND, M6	0.50" (13)	11.00" (279)	0.50" (13)
STUDS (125/150A)	15.99" (406)	6.40" (163)	4.50" (114)	5.12" (130)	13.00" (330)	6.60" (168)	3.30" (84)	1.65" (42)	3.30" (84)	3.50" (89)	1.00" (25)	Ø 0.59"x0.25",4x (Ø 15.2x6.4, 4x)	STUD, M10, 8x	STUD, GND, M10	0.53" (14)	14.69" (373)	0.64" (16)

TYPICAL TOLERANCE: +/-0.02" (0.50MM)



RPM8500

MIL/COTS 3-PHASE **DELTA** EMI POWER LINE FILTER

TYPICAL INSERTION LOSS, dB (50/50 Ohm)

Amps	Freq (MHz)	0.15	0.5	1.0	10	30
5	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30
10	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30
20	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30
30	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30
50	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30
70	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30
125	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30
150	CM (dB)	30	48	52	48	35
	DM (dB)	40	55	55	45	30

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[RPM8500-30-S](#) [RPM8500-5-S](#) [RPM8500-20-S](#) [RPM8500-10-S](#) [RPM8500-50-S](#) [RPM8500-70-S](#) [RPM8500-125-S](#)
[RPM8500-150-S](#)