

4

3


2

1

D


65.5 MAX

36.0 MIN



C

27.0 MAX



ALL DIMENSIONS ARE IN mm

SPECIFICATIONS

B

B

- 1. EFFECTIVE LENGTH, L_e (MM): 151
- 2. EFFECTIVE AREA, A_e (MM²): 308
- 3. EFFECTIVE VOLUME, V_e (MM³): 46525
- 4. TYPICAL WEIGHT: 0.23 KG
- 5. PERMEABILITY: 7K
- 6.
- 7. DIELECTRIC WITHSTAND (COATING): 2000VDC
- 8. COATING TO BE FREE FROM CRACKS/CHIPS

A

A

APPROVALS				DATE	RP RADIUS POWER <small>AN ALBUQUERQUE COMPANY</small>
DRN	AS			121012	
ECR	KO			121012	
REV	EC	DESCRIPTION	ORIG	APPR	
					PART NAME: FERRITE TOROID 8828028 COATED
CONFIDENTIAL DOCUMENT					SIZE: SHEET: D 10F1
					DRAWG. NO. 8810-017

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[5510-017](#)