




SPECIFICATIONS


- 1. CASE:  
22 GA. (.030) CRS, TIN PLATED
- 2. RATED CURRENT:  
60A
- 3. RATED VOLTAGE:  
60VDC
- 4. TEST VOLTAGE:  
LINE TO GROUND: 150VDC



INSERTION LOSS (50 Ω TYPICAL)

	.05 MHz	.15 MHz	.50 MHz	1.5 MHz	5.0 MHz	20 MHz
L/G	40 db	60 db	60 db	60 db	60 db	50 db

SCHEMATIC



NEXT ASSY	USED ON
APPLICATION	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ±.030 ± .XXX ±.010	CONTRACT NO.		FILTER CONCEPTS INC.				
	APPROVALS						DATE
	DRAWN GIANG TRINH		07-18-02	APPLICATION DRAWING DS60 FILTER			
	CHECKED DANNIEL VUONG		09-23-02				
	MATERIAL			SIZE B	CODE IDENT NO.	DRAWING NO. 7446	
FINISH			SCALE 1/1		SHEET 1	OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[DS60](#)