




SPECIFICATIONS


- 1. CASE:
22 GA. (.030) CRS, TIN PLATED
- 2. RATED CURRENT:
7.5A
- 3. RATED VOLTAGE:
250VAC, 50/60Hz
- 4. TEST VOLTAGE:
LINE TO LINE: 1.7KVDC
LINE TO GROUND: 2.2KVDC
- 5. LEAKAGE CURRENT:
.8mA MAX. @ 250VAC, 50Hz



INSERTION LOSS (50Ω TYPICAL)

	.05 MHz	.15 MHz	.50 MHz	1.5 MHz	5.0 MHz	20 MHz
L/L	15 db	30 db	60 db	60 db	60 db	60 db
L/G	8 db	45 db	65 db	65 db	65 db	60 db

SCHEMATIC



REVISION			
LTR	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07-30-02	LE
B	REVISED MARKING	03-06-03	LE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ±.030 ± .XXX ±.010	CONTRACT NO.		FILTER CONCEPTS INC.				
	APPROVALS	DATE					
	DRAWN	GIANG TRINH	07-30-02	APPLICATION DRAWING SF7 FILTER			
	CHECKED	DANNIEL VUONG	07-30-02				
MATERIAL			SIZE	CODE IDENT NO.	DRAWING NO.		
FINISH			B		7469		
			SCALE	1/1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[SF7](#)