


BR5005L-G Thru. BR5010L-G

Reverse Voltage: 50 to 1000V

Forward Current: 50A

RoHS Device




Features

- Plastic case with heatsink for heat dissipation.
- Surge overload -500 Amperes peak.
- UL recognized file # E349301 

Mechanical Data

- Epoxy: UL 94V-0 rate flame retardant.
- Case: Molded plastic with heatsink integrally, mounted in the bridge encapsulation.
- Mounting position: Any
- Weight: 30 grams
- Terminals: Wire lead Ø 50mils.



Maximum ratings and electrical characteristics

Rating at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%

Parameter		Symbol	BR 5005L-G	BR 5011L-G	BR 5021L-G	BR 5041L-G	BR 5061L-G	BR 5081L-G	BR 5010L-G	Unit
Maximum Recurrent Peak Reverse Voltage		V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Bridge Input Voltage		V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage		V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Current for Resistive Load @T _c =55°C		I _(AV)	50							A
Peak Forward Surge Current , 8.3ms Single Half Sine-Wave Super Imposed On Rated Load		I _{FSM}	500							A
Maximum Forward Voltage Per Bridge Element at 25A Peak		V _F	1.1							V
Maximum Reverse Current at Rate DC Blocking Voltage	@ T _J =25°C	I _R	10							μA
	@ T _J =100°C		1000							
Typical Thermal Resistance (Fig.3)		R _{θJC}	2.0							°C/W
Operating Temperature Range		T _J	-55 to +150							°C
Storage Temperature Range		T _{STG}	-55 to +150							°C

Rating and Characteristics Curves (BR5005L-G Thru. BR5010L-G)

Fig.1 - Derating Curve Output Rectified Current




Fig.2 - Maximum Forward Surge Current




Fig.3 - Typical Forward Characteristics






Fig.4 - Typical Reverse Characteristics



Marking Code

Part Number	Marking code
BR5005L-G	BR5005L
BR501L-G	BR501L
BR502L-G	BR502L
BR504L-G	BR504L
BR506L-G	BR506L
BR508L-G	BR508L
BR5010L-G	BR5010L



X / XX = Product type marking code

Standard Packaging

Case Type	BULK PACK	
	BOX (pcs)	CARTON (pcs)
BR-L	60	120

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[BR5005L-G](#)