







P.C.B. HOLE DRILLINGS



RoHS compliant

Part no.	Finish Pos. 1	Finish Pos. 2	Finish Pos. 3	Finish Pos. 4/5
131A25519X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
131J25519X	min. 50µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 10:1		
				date			material: COPPER ALLOY (Pos. 1 - 5)		
				drawn	15.06.15	Lehmenkühler		title: COAXIAL CONTACT PLUG 50 Ohm Solder termination 90° with 5 pins for D-SUB COMBINATION	
				appd.	15.06.15	Schmidt			
				norm					
d-old				dwg no:		DIN-A3 sh: 1			
a	Original								
rev.	description	date	name						
				part no:		SEE TABLE			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[131J25519X](#)