




Part no.	Finish Pos.1	Finish Pos.2	Finish Pos.3	Finish Pos. 4/5
131J35019X	min. 50µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
131A35019X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 5:1				
							material: see table				
								date	name	title: COAXIAL CONTACT PLUG 75 OHM Solder termination 90° with 3 pins for D-SUB COMBINATION	
								drawn 07.04.06	Lehmenkühler		
								appd. 07.04.06	Mickenbecker		
				norm							
				d-old		dwg no:		DIN-A3 sh: 1			
2 x b	Ä4600	14.01.2013	K.H.								
a	Original										
rev.	description	date	name			part no:  see table					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

131J35019X