





(b) STRIPPING DIMENSION



(b)

plating item 1	part no.
GOLD FLASH over NICKEL	132A10049X
30µin HARD GOLD over min. 50µin NICKEL	132C10049X

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	GOLD
1	1	MATING SIDE	COPPER ALLOY	SEE TABLE
pos	qty	description	material	plating
partlist				
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND			tolerance	scale: 5:1
			dim. in mm	material: see partlist
			date	name
			drawn 23.03.1998	Barcinski
			appd. 23.03.1998	Mickenbecker
			norm	
			d-old	13K2IE6A
5 x b	A5637	05.05.15	M.H.	title: HIGH POWER CONTACT FEMALE SOLDER CUP 40A D-SUB COMBINATION dwg no: (b) 13K1IE6A part no: see table
a	Original			
rev.	description	date	name	
CONEC®				DIN-A3 sh: 1

RoHS compliant

(b)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[132A10049X](#)