



STRIPPING DIMENSION



Directive 2002/95/EC RoHS compliant

plating	part no.
GOLD FLASH over NICKEL	132A10029X
30µin HARD GOLD over min. 50µin NICKEL	132C10029X
50µin HARD GOLD over min. 50µin NICKEL	132J10029X

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED					
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL					
1	1	FRONT SIDE	COPPER ALLOY	SEE TABLE					
pos	qty	description	material	plating					
partlist									
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND			tolerance		scale: 5:1				
			ISO 2768-m		material: see partlist				
			 dim. in mm		title:				
					HIGH POWER CONTACT FEMALE				
					SOLDER CUP 20A				
					drawn	23.03.98	Barcinski	D-SUB COMBINATION	
					appd.	23.03.98	Mickenbecker		
					norm				
					d-old				
	1 x b	Ä4820	02.07.2013	K.H.			dwg no:		DIN-A3
a	Original			13K11E4A			sh: 1		
rev.	description	date	name	part no: see table					

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[132C10029X](#)