









Directive 2002/95/EC
RoHS
Compliant

NOTES:

- HOOD: PBT GF UL 94 V0
- SCREW 4-40 UNC: STEEL; NICKEL PLATED
- SCREW FOR STRAIN RELIEF: STEEL; NICKEL PLATED
- COVER SCREW: STEEL; NICKEL PLATED
- STRAIN RELIEF: STEEL; NICKEL PLATED
- FEMALE CONNECTOR 7W2, CRIMP STYLE WITH WIRE BRIDGE AWG 22
SIGNAL CONTACTS: COPPER ALLOY; 7,5A nominal
PLATING: 30µm HARD GOLD over min. 50µm NICKEL
FEMALE CONTACTS WIRE BRIDGE FROM POS. 1 TO POS. 2

POS. 1



2x SCREW 4-40 UNC
with phillips head

POS. 2



1x CABLE STRAIN RELIEF

POS. 3



2x COVER SCREW

POS. 4



2x CABLE STRAIN RELIEF SCREW

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	ISO 2768-m
dim. in mm	
drawn	12.08.08 Schmidt
appd.	12.08.08 Kühle
norm	
d-old	

scale:	2:1
material:	see notes
title:	PLASTIC HOOD, straight cable exit with 7W2 Female Crimp Connector with wire bridge
dwg no:	Inventor 10
part no:	13K1A2569
	13-000241

CONEC

DIN-A3
sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[13-000241](#)