





pin assignment:

- 1) white
- 2) brown
- 3) green
- 4) yellow
- 5) red
- 6) blue
- 7) grey
- 8) pink
- 9) -

part-no.:	length L:	cable:
15-008243	2m	LiYCY (TP) 4x2x0,25mm² UL2464 cable: 781-GAQ280T
15-008253	4m	
15-008263	5m	

NOTES:

1. IP RATING: IP 20
2. METAL SHELL: ZINC DIE CAST;
min. 50µin NICKEL PLATING over COPPER
3. INSULATORS: PBT GF UL 94 V-0; BLACK
4. SEALING COMPOUND: EPOXY RESIN UL 94 V-0; BLACK
5. CONTACTS: COPPER ALLOY; GOLD FLASH over NICKEL
6. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. HEXLOCKING SCREWS: STAINLESS STEEL
8. OVERMOLDING: TECHNO MELT; BLACK
9. RECOMMENDED TORQUE FOR MOUNTING SCREW
35Ncm (3.1 in.LB) / max.67Ncm (6 in.LB)
10. CONNECTOR IS PART MARKED: [PART NO. CONEC ABC]

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		

tolerance			dim. in mm
date	name		
drawn 19.02.2016	Heinrich		
appd. 26.02.2016	Fischer		
norm			
d-old			



scale: 2.1 (4:1)	
material: SEE NOTES	
title: D-SUB FEMALE 9pos. MOLDED with open 4-40 UNC thread	
dwg no: 15K1A1706	DIN-A3
part no: SEE TABLE	
sh: 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[15-008243](#)