





pin assignment:

- 1) white
- 2) brown
- 3) green
- 4) yellow
- 5) red
- 6) blue
- 7) grey
- 8) pink
- 9) -

part-no.:	length L:	cable:
15-008243	2m	LiYCY (TP) 4x2x0,25mm² UL2464 cable: 781-GAQ280T
15-008253	4m	
15-008263	5m	

NOTES:

1. IP RATING: IP 20
2. METAL SHELL: ZINC DIE CAST; min. 50µin NICKEL PLATING over COPPER
3. INSULATORS: PBT GF UL 94 V-0; BLACK
4. SEALING COMPOUND: EPOXY RESIN UL 94 V-0; BLACK
5. CONTACTS: COPPER ALLOY; GOLD FLASH over NICKEL
6. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. HEXLOCKING SCREWS: STAINLESS STEEL
8. OVERMOLDING: TECHNO MELT; BLACK
9. RECOMMENDED TORQUE FOR MOUNTING SCREW 35Ncm (3.1 in.LB) / max.67Ncm (6 in.LB)
10. CONNECTOR IS PART MARKED: [PART NO. CONEC ABC]

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2.1 (4:1)				
							material: SEE NOTES				
								date	name	title: D-SUB FEMALE 9pos. MOLDED with open 4-40 UNC thread	
								drawn 19.02.2016	Heinrich		
								appd. 26.02.2016	Fischer		
				norm							
				d-old			dwg no:		DIN-A3		
	a	Original					15K1A1706		sh: 1		
rev.	description	date	name	part no: SEE TABLE							



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[15-008263](#)