


1


used for: D-SUB



Wire size AWG	Crimp height A
28	0,61 – 0,76
26	0,66 – 0,81
24	0,66 – 0,86



STRIPPING DIMENSIONS




NOTES:

- ⑥ Material: Phosphor Bronze
Finish: Gold Flash over Nickel in the Contact Area
Temperature Range: -55°C to +125°C
Rated Current: 5.0A
Contact Resistance: $\leq 10\text{m}\Omega$
Length of Reel—small Reel Wheeled Right: 500 Contacts
Crimping: Use Crimp Tool 360X10079X

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

finish:				tolerance		 dim. in mm	
				2010	date	name	
				drawn	03.12.	Henneboel	
				appd.	03.12.	Koch	
				norm			
				d-old			
1 x b	Ä 4116	26.09.2011	Lehmen.				
a	Original						
rev.	description	date	name				

dim. in mm

scale:	5:1
material:	SEE NOTES

title: SOCKET CONTACT CRIMP AWG 28-24 (small spool wheeled right)

dwg no:	AutoCAD 2006	DIN-A
16K1A2747		4
		sh: 1/1
part no:	162A11879X	

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[162A11879X](#)