

4				3				2				1																																
								used for: D-SUB HD																																				
												<table><tr><th>Part NO.</th><th>POS.</th><th>A -0.76</th><th>B -0.25</th><th>C</th></tr><tr><td>164A17009X</td><td>15</td><td>31.19</td><td>16.46</td><td>25.00 +0.12/-0.13</td></tr><tr><td>164A17019X</td><td>26</td><td>39.52</td><td>24.79</td><td>33.30 +0.15/-0.1</td></tr><tr><td>164A17029X</td><td>44</td><td>53.42</td><td>38.50</td><td>47.04 ±0.13</td></tr><tr><td>164A17039X</td><td>62</td><td>69.70</td><td>54.96</td><td>63.50 ±0.13</td></tr></table>				Part NO.	POS.	A -0.76	B -0.25	C	164A17009X	15	31.19	16.46	25.00 +0.12/-0.13	164A17019X	26	39.52	24.79	33.30 +0.15/-0.1	164A17029X	44	53.42	38.50	47.04 ±0.13	164A17039X	62	69.70	54.96	63.50 ±0.13				
Part NO.	POS.	A -0.76	B -0.25	C																																								
164A17009X	15	31.19	16.46	25.00 +0.12/-0.13																																								
164A17019X	26	39.52	24.79	33.30 +0.15/-0.1																																								
164A17029X	44	53.42	38.50	47.04 ±0.13																																								
164A17039X	62	69.70	54.96	63.50 ±0.13																																								
Directive 2002/95/EC RoHS compliant																																												
<table><tr><td colspan="4">APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL</td></tr><tr><td colspan="4">CUSTOMER APPROVAL DATE:</td></tr><tr><td colspan="2">NAME:</td><td colspan="2">TITLE:</td></tr><tr><td colspan="4">COMPANY NAME:</td></tr><tr><td colspan="4">APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL</td></tr></table>												APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL				CUSTOMER APPROVAL DATE:				NAME:		TITLE:		COMPANY NAME:				APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL				NOTES: 1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin Nickel 2. INSULATORS: PBT GF UL 94 V-0, BLACK 3. CONTACTS: COPPER ALLOY PLATING: GOLD FLASH over NICKEL SOLDER CUP ACCEPTS CABLE AWG 22 4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC												
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL																																												
CUSTOMER APPROVAL DATE:																																												
NAME:		TITLE:																																										
COMPANY NAME:																																												
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL																																												
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND																																												
CONEC CORPORATION BRAMPTON, ONTARIO												tolerance																																
												dim. in mm																																
scale: 2:1												material: SEE NOTES																																
title: D-SUB HD FEMALE 15-62pos. SOLDER CUP																																												
dwg no: AutoCAD 2000												DIN-A 4																																
part no: SEE TABLE																																												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[164A17009X](#) [164A17019X](#) [164A17029X](#) [164A17039X](#)