

4

3

2


1

F


F

E

E





used for: D-SUB HD



P.C.B. HOLE PATTERN

D

D



C

C

NOTES:

1. METAL SHELLS: STEEL; TIN PLATED
2. INSULATORS: PA GF; UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY
4. PLATING: HARD GOLD OVER NICKEL
5. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS

Directive 2002/95/EC
„RoHS“
Compliant

B

B


A

A

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance



scale:

2:1

material:

SEE NOTES

title:

D-SUB HD FEMALE

15pos. Pin Version

threaded rear spacer, front threaded lock

dwg no:

CAD/ REL.14

DIN-A

16K1IJVA

4

sh: 1/1

product no:

164A17309X

CONEC[®]

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[164A17309X](#)