







NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY; PLATING (SEE PART NO):
☐ PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
☐ PLEASE ADD B for 20µin HARD GOLD over min. 50µin NICKEL
☐ PLEASE ADD C for 30µin HARD GOLD over min. 50µin NICKEL
- METAL BRACKETS:
 ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- FIXING PLATE: PBT GF UL 94 V-0, BLACK
- PCB-SNAPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
 PCB-HOLE: Ø3,1±0,1mm; PCB-THICKNESS: 1,6mm
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKET: 164□19929X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1		
							material: see notes		
					date	name	title: D-SUB DUAL PORT 19,05mm FEMALE / FEMALE 2x15pos. threaded insert, metal bracket, fixing plate, snap		
					drawn 10.04.13	Schmidt			
					appd. 10.04.13	Fischer			
					norm				
					d-old	16K1A543 / 16K1IMGA			
	1 x b	Ä717	10.04.13	HS			dwg no:		DIN-
	a	Original					16K1A3220 (b)		A3
	rev.	description	date	name			part no: 164□19929X (see note3)		sh: 1



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 3:1	
								material: see sheet 1	
						date	name	title: P.C.B. HOLE DRILLINGS D-SUB DUAL PORT 19,05mm FEMALE / FEMALE 2x15pos.	
					drawn	10.04.13	Schmidt		
					appd.	10.04.13	Fischer		
					norm				
					d-old	see sheet 1		dwg no: 16K1A3220	
	a	Original							
	rev.	description	date	name				part no: see sheet 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)
[164A19929X](#)