



used for: D-SUB



⑥ 9 pos.



15-37 pos.




SEE DETAIL VIEW



DETAIL VIEW

⑥ SCREW LOCK



No. of pos.	A	B	C	D	E	F	Part No:
9	34.0	25.0	25.0	27.75	14.5	8.5	165X11009X
15	42.3	33.3	37.0	39.75	14.5	10.0	165X11019X
25	56.0	47.0	37.0	39.75	14.5	10.5	165X11029X
37	72.5	63.5	37.0	39.75	14.5	10.5	165X11039X

⑥

Directive 2002/95/EC
"RoHS"
Compliant

NOTES:

- HOOD MATERIAL: ABS V0 / METALLIZED
- SCREWLOCK: MATERIAL: BRASS NICKEL-PLATING

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
5 x b	Ä 2286	02.08.2005	HS

tolerance	dim. in mm
2002	date
drawn	04.03. Schmidt
appd.	04.03. Mickenbecker
norm	
d-old	KATIIYSA
CONEC®	

scale:	1:1
material:	SEE NOTES
title:	
PLASTIC HOOD with staight cable exit and screw lock, 9-37 pos. ⑥	
dwg no:	AutoCAD 2000 DIN-A
16K1A670	
part no:	SEE TABLE
sh: 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X11039X](#)